



Job Name:

Job Type:

Comments:

Quantity:

40012-773: Four-Light Wall/Bath

Dimensions:

Width: 24 3/4"

Extends: 8 1/4"

Height: 7 3/4"

Wire: 6 1/2"

Mounting Proc.: Center Lock-Up

Connection: Mounted To Box



Bulbs:

- 4 - medium A - Line 100w Max. 120v - Not included
- 4 - LED Medium LED A-19 8w 120v - Not included
- 4 - LED Medium LED A-19 13.5w 120v - Not included

Features:

- Fixture may be mounted in the up or down position

Material List:

1 Arms - Steel - Two Tone Nickel

Safety Listing:

UL Listed for Damp Locations
cUL Listed for Damp Locations

Instruction Sheets:

English (HC-753)
French (F-007)

Collection: Alexandria

Four Light Bath Bar in Two Tone Nickel Finish with Glass Shades.

Wall/Bath fixture with two-tone nickel finish and clear highlighted etched glass.

Design #: D20078

UPC #:785652400124

Finish: Two Tone Nickel (773)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Glass	Clear Highlighted Satin Etched	1					5 1/4				

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Back Plate					4 1/4	3 1/2

Replacement Bulb Data:

Product #	Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97308S	A-19	E-26 Medium			120v	50000	425	3000	85
97309S	A-19	E-26 Medium			120v	50000	850	3000	85

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	UPS Ship
Individual	40012-773	1	785652400124	23.5	9.25	10.5	1.321	10.4	Yes
NJ Pallet		48		48	40	69.75	77.5	499.2	No
NV Pallet		48		48	40	69.75	77.5	499.2	No

