

Full-Sized Contemporary Floating Cloud RC/CSW

Features

The molded white cloud diffuser has rounded corners and edges for a soft pillow appearance. It can be used in various applications including corridors, kitchens and public spaces. Fixture mounts to standard junction box (not included).

Construction

Housing is die-formed of 22-gauge steel. Standard mounting holes are included. Power supply connections can be made inside the fixture wire way or in a junction box (not included).

Finish

Back plate is finished in lighting grade white baked gloss enamel paint.

Diffuser

Diffuser is made of white acrylic plastic. Four clips on the two edges of the diffuser allow it to lift and shift for easy removal.

Electrical

This unit can be ordered in the following options: with UL listed instant-start, electronic high power factor ballast; 120V 60Hz AC (E8 suffix), 120-277 Universal 50/60Hz AC (MV suffix).

R8 model number suffix designates normal power factor, 120V, residential grade ballast.

Lamping

For use with 2/32, 4/32 or 4/17 watt T8 linear fluorescent lamps; supplied by others.

Certification

All fixtures are cULus listed for damp locations.

Options (consult factory)

120-277V HPF



Dimming

ENERGY STAR qualified with 120V ballast

Emergency battery back-up

Specifications and dimensions
subject to change without notice.

Project		Fixture Type
Location		Quantity
Approved By	Date	Catalog Number



Ordering Information:

Model No.		Lamps		Dimensions			Mounting
White Diffuser	White Housing	Qty	Lamp	H	W	L	M
RC14	CSW142E8	2	F32T8	6"	15"	51-3/4"	39-15/16"
RC14	CSW144E8	4	F32T8	6"	15"	51-3/8"	39-15/16"
RC22	CSW2U4E8	2	FB32T8	6"	27"	27-1/2"	13"
RC22	CSW224E8	4	F17T8	6"	27"	27-1/2"	13"
RC24	CSW244E8	4	F32T8	6"	27"	51-1/2"	45-3/8"