


## ELBOW - 90°

FIG. 5101

GROOVED FOR BRAZING RING



- GROOVED
- Fig. 5101 - FF X FF
- Fig. 5102 - FF X FEM

- FACE FED
- Fig. 5001 - FF X FF
- Fig. 5002 - FF X FEM



^ CONSULT FACTORY / \* INDICATES TYPE A

### ALL DIMENSIONS IN INCHES

| FIG  | SIZE CODE | IPS    | A       | B | C | X       | Y | Z | WEIGHT |
|------|-----------|--------|---------|---|---|---------|---|---|--------|
| 5101 | 040       | *1/4   | 23/32   | - | - | 7/16    | - | - | 0.05   |
| 5101 | 060       | *3/8   | 13/16   | - | - | 1/2     | - | - | 0.1625 |
| 5101 | 100       | *1/2   | 1       | - | - | 5/8     | - | - | 0.232  |
| 5101 | 150       | *3/4   | 1-3/16  | - | - | 25/32   | - | - | 0.293  |
| 5101 | 200       | *1     | 1-7/16  | - | - | 1       | - | - | 0.5587 |
| 5101 | 250       | *1-1/4 | 1-11/16 | - | - | 1-3/16  | - | - | 0.7217 |
| 5101 | 300       | *1-1/2 | 1-27/32 | - | - | 1-7/32  | - | - | 1.116  |
| 5101 | 400       | *2     | 2-1/8   | - | - | 1-15/32 | - | - | 1.7444 |
| 5101 | 450       | *2-1/2 | 2-11/16 | - | - | 1-29/32 | - | - | 2.8733 |
| 5101 | 500       | *3     | 3-3/32  | - | - | 2-1/4   | - | - | 4.1266 |
| 5101 | 550       | *3-1/2 | 3-7/16  | - | - | 2-9/16  | - | - | 5.296  |
| 5101 | 600       | *4     | 3-25/32 | - | - | 2-7/8   | - | - | 7.58   |
| 5101 | 650       | *5     | 4-1/2   | - | - | 3-1/2   | - | - | 15.06  |
| 5101 | 700       | *6     | 5-1/8   | - | - | 4-1/32  | - | - | 21.93  |
| 5101 | 750       | *8     | 6-9/16  | - | - | 5-1/4   | - | - | 46     |
| 5101 | 800       | *10    | 8-3/32  | - | - | 6-19/32 | - | - | 78.51  |
| 5101 | 820       | *12    | 9-1/2   | - | - | 7-7/8   | - | - | 131.83 |