





Table Top Electric Water Heaters features convenient flatsurface at 36" height, providing extra "counter space"wherever installed.

All plumbing and electrical connections are made through back of water heater. 27 and 40-gallon tank capacities. Equipped with PEXAN[™] cross linked PEX polymer dip tube.

Junior Electric Water Heaters feature compact design, versatile plumbing and electrical connections.

Designed for installation under a counter, in a crawl space or in other tight spaces. Tank capacities from 6 through 40 gallons. Single heating element standard.

Point-Of-Use Electric Water Heaters designed for lowdemand point-of-use applications, such as office lavatories or any building with remote restrooms.

2¹/₂-gallon tank capacity, with single heating element. Includes 110/120V cord set with 3-prong plug. Also includes integrated wall-mounting brackets for easy installation.

All Select Specialty Electric Water Heaters have foam insulation to protect against radiant heat loss.

- **Aluminum Anode Rod** Helps protect against corrosion for longer life.
- **Glasslined Tank** For long-lasting protection against corrosion.



- CSA Certified and ASME Rated T&P Relief Valve
- 6-Year Limited Tank and Parts Warranty

Code Compliance – Meets the Federal Minimum Energy Standards effective January 20, 2004, according to the National Appliance Energy Conservation Act (NAECA) of 1992 and meets the standby loss requirements of the U.S. Department of Energy and current edition of ASHRAE/IESNA 90.1 and current editions of ICC codes and HUD Standards.



For more information on the Specialty Electric Water Heaters contact: State Water Heaters 500 Tennessee Waltz Parkway, Ashland City, TN 37015 800 365-0024 Toll-free USA www.statewaterheaters.com

SOLID. STATE





© 2011 State Industries



000




| MODEL NUMBER | PEAK DEMAND OUTPUT (1st Hour Rating Gallons) | ENERGY FACTOR | GALLON CAPACITY | ELEMENT WATTAGE | | DECOVEDV | | DIMENSIONS IN INCHES | | | APPROXIMATE |
|---------------------|---|------------------|--------------------|------------------|-----------------|-----------------------|------------|----------------------|----------|---------------|------------------------------|
| | | | | STANDARD 240V | MAXIMUM 240V | RECOVERY 90°F RISE | R VALUE | A HEIGHT | В | C DIAMETER | SHIPPING WEIGHT (LBS.) |
| TABLE TOP MODELS | | | | | | | | | | | |
| P6 30 20T1 | 45 | .89 | 27 | 4500 | 6000 | 21 | 12 | 36 | 25 | 21 | 141 |
| P6 40 20T4 W | 52 | .88 | 40 | 4500 | 6000 | 21 | 12 | 36 | 25 | 24 | 174 |
| MODEL NUMBER | PEAK DEMAND OUTPUT (1st Hour Rating Gallons) | ENERGY FACTOR | GALLON CAPACITY | ELEMENT WATTAGE | | RECOVERY | | DIMENSIONS IN INCHES | | | APPROXIMATE |
| | | | | STANDARD 120V | MAXIMUM 240V | 90°F RISE | R VALUE | A HEIGHT | B T&P | C DIAMETER | SHIPPING WEIGHT (LBS.) |
| JUNIOR MODELS | | | | | | | | | | | |
| ES6 6 SOMS | N/A | N/A | 6 | 1650 | 3000 | 8 | 8 | 15-1/4 | 10-3/4 | 14-1/8 | 31 |
| ES6 10 SOMS | N/A | N/A | 10 | 1650 | 6000 | 8 | 8 | 18-1/4 | 12-1/4 | 16 | 45 |
| ES6 20 SOMS | N/A | N/A | 19 | 1650 | 6000 | 8 | 8 | 25 | 18-1/2 | 18 | 65 |
| ES6 20 SOMT | N/A | N/A | 19.9 | 1650 | 6000 | 8 | 8 | 31-3/4 | 25-3/4 | 16 | 62 |
| ES6 30 SOMS K | 37 | .93 | 29 | 1650 | 6000 | 8 | 16 | 30 | 22-1/2 | 22 | 111 |
| ES6 40 SOMNS K | 43 | .92 | 38 | 1650 | 6000 | 8 | 12 | 31-1/8 | 24-5/8 | 23 | 125 |
| POINT-OF-USE MODELS | | | | | | | | | | | |
| ES6 2 SSUS K † | N/A | N/A | 2.5 | 1500 @ 120V | | 7 | 8 | 13-3/4 | 11 | 13-3/4 | 18 |

Recoveries are rounded to nearest gallon

Water Connections – 3/4" on Table Top and Junior models, 1/2" NPT on Point-of-Use models

+Top mounted T&P adds approximately 3" additional to overall height



State Industries, Inc. reserves the right to make product changes or improvements without prior notice.

For more information on the Specialty Electric Water Heaters contact: State Water Heaters 500 Tennessee Waltz Parkway, Ashland City, TN 37015 800 365-0024 Toll-free USA www.statewaterheaters.com

SOLID. STATE



SRESS00107 Revised October 2011