

# SELECT<sup>®</sup>

## Residential Electric Water Heaters



**Tall, Short and Lowboy models available.**

**Self-Cleaning Diffuser Dip Tube** - Helps reduce lime and sediment buildup, maximizes hot water output. Made of State PEXAN<sup>™</sup>, a cross-linked PEX polymer that can withstand long-term exposure to water temperatures up to 400°F.

**Aluminum Anode Rod** - Helps protect against corrosion for longer life.

**Durable Tamper-Resistant Brass Drain Valve**

**Glasslined Tank** - For long-lasting protection against corrosion.

**CSA Certified and ASME Rated T&P Relief Valve** -  
Top-mounted T&P Relief Valve available as option on some models.

**Compliance** - Meets the Federal Energy Efficiency Standards effective January 20, 2004, according to the National Appliance Energy Conservation Act (NAECA) of 1992 and meets the standby loss requirements of the U.S. Department of Energy and current edition of ASHRAE/IESNA 90.1 and ICC and HUD Standards.

**6-Year Limited Tank and Parts Warranty Code**

**Upgrade Tank Warranty to 10 Years** - See details on page 2.



Low Lead Content



For more information on Select<sup>®</sup> contact:  
State Water Heaters  
500 Tennessee Waltz Parkway, Ashland City, TN 37015  
**800-365-0024 Toll-free USA**  
[www.statewaterheaters.com](http://www.statewaterheaters.com)

**SOLID.STATE.**



# SELECT®

## Residential Electric Water Heaters



MODEL NUMBER	SERIES	PEAK DEMAND OUTPUT (1st Hour Rating Gallons)	ENERGY FACTOR	GALLON CAPACITY	ELEMENT WATTAGE 240 VAC		RECOVERY 90°F RISE	R VALUE	DIMENSIONS IN INCHES			APPROX. SHIPPING WEIGHT (LBS)
					STANDARD	MAXIMUM			A HEIGHT	B DIAMETER	C	
<b>TALL MODELS</b>												
ES6 30 DORT	200	43	.93	30	4500	6000	21	16	46-1/2	18	39-1/2	90
ES6 40 DORT	200	52	.92	40	4500	6000	21	16	59-1/2	18	53-1/2	106
ES6 52 DORT	210	60	.91	50	4500	6000	21	16	54	20	47-1/2	116
ES6 55 DORT	210	67	.90	55	4500	6000	21	16	60-1/4	20	52-3/4	134
ES6 66 DORT	210	72	.88	66	4500	6000	21	16	60-1/4	20-1/2	53	178
ES6 80 DORT	210	81	.86	80	4500	6000	21	16	60-1/2	22-1/2	52	208
ES6 120 DORT *	200	112	.81	119	4500	6000	21	16	64-1/4	28	54-1/4	326
<b>SHORT MODELS</b>												
ES6 30 DORS	200	43	.93	30	4500	6000	21	16	36-1/2	20-1/2	28	90
ES6 40 DORS	200	52	.92	40	4500	6000	21	16	44	20-1/2	37-3/4	103
ES6 50 DORS	210	62	.90	50	4500	6000	21	16	48	21-1/2	40-1/2	121
<b>LOWBOY MODELS</b>												
ES6 30 DOLS	200	41	.93	29	4500	6000	21	16	30	22	22-1/2	91
ES6 40 DOLNS	200	48	.92	38	4500	6000	21	12	31-1/4	23	24-5/8	113
ES6 40 DOLBS**	200	48	.93	38	4500	6000	21	16	32-1/4	24	24-5/8	118
ES6 50 DOLS	200	55	.91	50	4500	6000	21	16	34	26-1/2	25	164

Recoveries are rounded to nearest gallon


Water Connections - 3/4" on all models

For 10-Year Tank Warranty, change "6" to "X" in Model Number (ESX 40 DORT)

\*This model is not available with top-mounted T&P Valve

10-Year Tank Warranty and top T&P Valve option combo not available on ES6 40 DOLNS and ES6 50 DOLS

\*\*Heater ships with supplied insulation blanket



\*Location for optional top-mounted T&P Valve, if available and ordered from factory.

For complete information on limited warranties, consult written warranty, or contact the State Customer Care Center, 1-800-365-0024.

State Industries, Inc. reserves the right to make product changes or improvements without prior notice.

For more information on Select® contact:  
 State Water Heaters  
 500 Tennessee Waltz Parkway, Ashland City, TN 37015  
 800-365-0024 Toll-free USA  
 www.statewaterheaters.com

**SOLID.STATE.**

