




TAG:

Architect/Engineering Specifications:

8" deck mount mixing faucet with chrome plated brass body, 10" swing nozzle with garden hose male vacuum breaker outlet, compression cartridges with spring checks, 4" wrist action handles, chrome plated escutcheon, 60" flexible stainless steel hose with heat resistant handle, self-closing angled spray valve, deck flange hose guide and extended 1/2" NPSM male inlets. Certified to ASME A112.18.1/CSA B125.1, NSF 61-Section 9, NSF 372 and ASSE 1011.



Features & Benefits:

- 8" deck mount mixing faucet w/ chrome plated brass body
- 10" swing nozzle with garden hose male vacuum breaker outlet
- Quarter-turn Eterna compression cartridges with spring checks to prevent cross flow of water
- 4" wrist action handles w/ color coded indexes
- Removable brass seats
- · Chrome plated escutcheon
- 60" flexible stainless steel hose w/ heat resistant blue handle and hold down ring
- · Self-closing angled spray valve
- Deck flange hose guide
- 1/2" NPT male inlets
- Tailpieces and nuts for 1/4" NPT male connections
- Material: Chrome plated brass body, tubular spout, spray valve body & deck flange, stainless steel hose and chrome plated metal handles & escutcheon

Optional Handles

□ 4" Wrist Action (Standard) □ Lever



□ B-0107 (1.42 GPM) □ B-0107-C (0.65 GPM) □ B-0107-J (1.07 GPM) □ B-0108 (1.07 GPM) □ B-0108-C (0.65 GPM)

Product Compliance:

- ASME A112.18.1 / CSA B125.1
- NSF 61 Section 9
- NSF 372 (Low Lead Content)
- EPAct 2005 Non-Compliant (PRSV)
- ASSE 1011 (VB)

Warranty: One Year (Limited)

Performance Data:

- Pressure: 20 125 psi
- Temperature: 40 °F 140 °F
 - Flow Rate: Faucet: 3.86 GPM @ 60 psi Spray Valve: 2.11 GPM @ 60 psi

Optional Cartridges

Quarter-Turn Cerama w/ Check Valve
Quarter-Turn Eterna w/ Spring Check (Standard)







