Electronic Faucet - 591T Series 4" Cast Lavatory





Specification: (example)

- 102mm (4") electronic faucet
- **CAST** one-piece body with integral waterproof sensor and connector
- Polished chrome plated trim
- Battery (4 'C' cell) or Hardwire (24VAC) infrared electronic handwash
- $H_2OPTICS^{TM}$ technology no external adjustments required
- Adjustable sensing range and timeout
- Audible low battery indicator

- Serviceable filter screen upstream of the valve
- Metal hold-down package Tempered water supplied to solenoid valve, (except control box options No. 0 and 1)

and...

with... (specify battery or hardwire)

with... (add outlet required)

with... (add control box required)

with... (transformer - specify separately - See Back Page)





Engineer/Architect Approval	
Model Specified:	
Approval:	Date:

DESCRIPTION	PRODUCT NO.		
Hardwire	591T02		For Chrome
	591T02	- SS	For Brilliance® Stainless Steel
Battery Operated	591T12		For Chrome
1 .	591T12	- SS	For Brilliance® Stainless Steel





SPOUT & SENSOR		OUTLET		CONTROL BOX
	✓		<u> </u>	✓
o		0		Base Model with Surface Mount Housing* SEE Specification Drawing #1
1		1		For RECESSED MOUNTING Components ASSEMBLED in 10" Box w/S/S Cover.* SEE Specification Drawing #2
2 4" CAST Lavatory Spout		Vandal Resistant 1.5 USGPM (5.7 L/min.) Laminar w/Agion® Antimicrobial		2
3		Vandal Resistant 1.5 USGPM (5.7 L/min.) Flow Control Aerator		3
4		Standard 1.5 USGPM (5.7 L/min.) Flow Control Aerator		4
5		Vandal Resistant 0.5 USGPM (1.9 L/min) Flow Control Non- Aerating Spray Outlet		5
6		Vandal Resistant 1.0 USGPM (3.8 L/min) Flow Control Non- Aerating Spray Outlet		For RECESSED MOUNTING Components & Mechanical Mixing Valve (1) ASSEMBLED in 10" Box w/S/S Cover. SEE Specification Drawing #3
7		7		7
8		8		For RECESSED MOUNTING Components & Thermostatic Mixing Valve ASSEMBLED in 10" Box w/S/S Cover. SEE Specification Drawing #4
9		9		9

(1) With Thermostatic Limit Stop.

Flowrates are at 60 PSI.

Refer to www.specselect.com for individual models. Note: Use this page front and back, with specification drawing page referenced above, as product submittal sheets.

^{*} Mixing Valve supplied by others.



TECK®

Electronic Faucet - 591T Series 4" Cast Lavatory

Approvals:

- CSA certified
- Complies to ASME A112.18.1
- ADA Compliant and meets Handicapped Accessibility Standard ASME A117.1 of less than 5 lbs. handle operating force.
- IAPMO listed
- Control Box Option 6 Mechanical Mixing Valve CSA certified
- Control Box Option 8 Thermostatic Mixing Valve CSA certified and meets ASSE 1016 and ASSE 1017

(Contact Delta Representative for State and/or Local Approvals.)

U.S. Patent # 6, 826, 455

FLOWRATE vs PRESSURE FLOW FLOW **Outlet Flowrates** (USGPM) 2.5 8-2 7 20 70 ΙÖ 30 40 50 60 ก่ห Line Pressure (psig) **Spout Outlets** No. 2 Laminar Flow Outlet No. 3 & 4 Aerator No. 5 Low Flow Outlet ■ No. 6 Flow Control Outlet


CAST SPOUT	"D"			
OUTLET NO.	mm	in.		
2	П	0.45		
3	11	0.45		
4	- 11	0.45		
5	- 11	0.45		
6	11	0.45		

OPERATION:

- Hands free (touchless) operation.
- Water flows when sensor is activated.
- Water flow stops upon de-activation of sensor.
- Auto shut-off feature that is selectable between 15 to 75 seconds. Factory set to 45 seconds. Will reset once obstruction is removed.
- Adjustable sensing distance 76 to 381mm (3" to 15") factory set to 229mm (9") (+/- 1.0")
- Low battery audible beep (for battery models only). Will activate after faucet shuts off when approximately 1500 cycles remain.

NOTE: For optimum performance of this product, we recommend a system pressure between 20 and 80 PSI static. This product will operate up toa maximum of 125 PSI static per ANSI and CSA requirements. However, we do not recommend pressures above 80 PSI. Thermal expansion or leaking pressure reducing valves may require use of expansion tanks or relief valves to ensure your system never exceeds its maximum intended pressure setting.

Note: Measurements may vary ± 6mm (0.25")



59IT ELECTRONIC FAUCET OPTIONAL ACCESSORIES:

/	TRANSFO	TRANSFORMERS:													
	060704A	110 to 24VAC Class II 20VA (Up to 5 Electronic Valves)													
	060771A	110 to 24VAC Class II 40VA (Up to 10 Electronic Valves)													
	060772A	110 to 24VAC Class II 100VA (Up to 25 Electronic Valves)													
/	CORDS:														
	060690A	36" Cable Extension													

Refer to www.specselect.com for individual models.

Product supplied as shown by solid lines. All items shown by dotted lines supplied by others.






BASE MODEL - SURFACE MOUNT

591T SERIES

/	PRODUCT NO.				VALVE TYPE	COVER
	591T	0	2	0	Deckmount Cast Lavatory Hardwire	Surface Mounted
	591T	I	2	0	Deckmount Cast Lavatory Battery	Surface Mounted






TEMPERED WATER - ASSEMBLED CONTROL BOX

591T SERIES

/	PRODUCT NO.					FAUCET TYPE	MOUNT TYPE	COVER		
	*591T	0	2		I	Deckmount Cast Lavatory Hardwire	Recessed Mount	305mm (12") Stainless Steel		
	*591T	I	2		I	Deckmount Cast Lavatory Battery	Recessed Mount	305mm (12") Stainless Steel		
	*This product is supplied with Flexible Sensor Cord Conduit on Recessed Mount Installations.									








MECHANICAL MIXING VALVE ASSEMBLED CONTROL BOX

591T SERIES

/	PRODUCT NO.					FAUCET TYPE	MOUNT TYPE	COVER		
	*591T	0	2		6	Deckmount Handwash Hardwire	Recessed Mount	305mm (12") Stainless Steel		
	*591T	I	2		6	Deckmount Handwash Battery	Recessed Mount	305mm (12") Stainless Steel		
	*This product is supplied with Flexible Sensor Cord Conduit on Recessed Mount Installations.									







THERMOSTATIC MIXING VALVE ASSEMBLED CONTROL BOX

591T SERIES

/	PRODUCT NO.					FAUCET TYPE	MOUNT TYPE	COVER		
	*591T	0	2		8	Deckmount Handwash Hardwire	Recessed Mount	305mm (12") Stainless Steel		
	*591T	I	2		8	Deckmount Handwash Battery	Recessed Mount	305mm (12") Stainless Steel		
	*This product is supplied with Flexible Sensor Cord Conduit on Recessed Mount Installations.									

