



Measurements:

|                       |                 |                  |
|-----------------------|-----------------|------------------|
| <u>Height</u>         | <u>Width</u>    | <u>Extension</u> |
| 9.00"                 | 23.50"          | 10.00"           |
| <u>BP Height</u>      | <u>BP Width</u> |                  |
| 5.75"                 | 5.75"           |                  |
| <u>Hanging Weight</u> |                 |                  |
| 5.84 lb               |                 |                  |

Lamping:

|                     |                    |
|---------------------|--------------------|
| Incandescent MB     | 3,450 Rated Lumens |
| 3.00 60W MB         | Color Temperature  |
| 180 total watt      | 2,500 Rated Life   |
| Dimmable : Standard |                    |

Shipping:

|                        |                     |                      |                      |
|------------------------|---------------------|----------------------|----------------------|
| <u>Carton Weight</u>   | <u>Carton Width</u> | <u>Carton Height</u> | <u>Carton Length</u> |
| 9.03 lb                | 10.50"              | 10.00"               | 25.00"               |
| <u>Master Pack Qty</u> | <u>UPC</u>          | <u>UPS</u>           |                      |
| 1.0000                 | 783209006010        | Yes                  |                      |

Finish:

Satin Nickel SN

Glass:

Soft Vanilla SV

Material:

Steel

Certification:

Damp Location  
Location

Additional:

MB (Not Included)  
Lighting Direction: Both