
# TAG:

# Flexible Stainless Steel Hose

### **Architect/Engineering Specifications:**

44" flexible stainless steel hose with heat resistant handle, 3/4-14 UN female outlet and 3/4-14 UN female inlet. Includes adapters for 1/4" and 3/8" NPT inlets. Certified to ASME A112.18.1/CSA B125.1, NSF 61-Section 9 and NSF 372.

Job Name	
Model Specified	Quantity
Variations Specified	
Date	





#### Features & Benefits:

- 44" flexible stainless steel hose with heat resistant gray handle
- 3/8" NPT male x 3/4"-14 UN male adapter included
- 1/4" NPT male x 3/4"-14 UN male adpater included
- Polyurethane inner tubing
- 3/4-14 UN female outlet
- 3/4-14 UN female inlet
- · Hose washers included
- Material: Polished chrome plated brass end fittings, thermoplastic handle and stainless steel hose

## **Product Compliance:**

- ASME A112.18.1 / CSA B125.1
- NSF 61 Section 9
- NSF 372 (Low Lead Content)

Warranty: Three Year (Limited)

#### **Performance Data:**

Pressure: 20 - 125 psi
Temperature: 40 °F - 140 °F
Flow Rate: 6.25 GPM @ 60 psi











