



Fieldpiece

New Relative Humidity Head


Model ARH4

- Measures Temp and RH%
- Calculates wet bulb and dew point temperatures


\$89 msrp

Specifications:

- Low battery indication: Red LED is lit when the voltage drops below the operating level.
- Output impedance: 500Ω approx.
- Operating environment: 32°F to 120°F (0 °C to 50 °C) at <95%RH.
- Storage temperature: -4°F to 140°F (-20°C to 60°C) <80%RH with battery removed.
- Range: 32°F to 140°F
- Accuracy: ±1°F (32°-113°F)
- Battery: 9V
- Dimensions: 146mm(H) x 67mm(W) x 32mm(D)
- Weight: 180g including battery approx.
- Warranty: 1 year



Add EHDL1 for a stand alone digital sling psychrometer, snap onto stick meter (HS series), or use AHDL1 for use in combination with most DMMs.



580 West Central Ave. Suite A
 Brea, CA 92821
 Phone: (714) 257-9060
 Fax: (714) 257-9069