



# Fluence®

## Frameless Pivot Shower Door

### K-702402-L

#### Features

- Frameless design highlights showering area.
- Two-roller compression latches allow for smooth secure door closure.
- A concealed hinge provides smooth, stable operation.
- No top header eliminates clearance issues.
- Frameless, 1/4" (6 mm) thick Crystal Clear tempered glass.
- Elegant inside and outside brass pull handles complete the look of this door.
- CleanCoat® technology creates a barrier between the water and glass to help keep your shower door looking new.

#### Material

- Anodized aluminum prevents rusting or corrosion.
- Tempered glass ensures maximum safety and durability.

#### Installation

- Out-of-plumb adjustability allows for simpler installation.
- Can be installed to open to the left or right.

#### Components

Additional included component/s: Hardware kit.



#### Codes/Standards

CPSC 16CFR 1201  
ANSI Z97.1 (Tempered Glass)



#### KOHLER® One-Year Limited Warranty

See website for detailed warranty information.

#### Available Color/Finishes

*Color tiles intended for reference only.*

| Color  | Code | Description             |
|--|------|-------------------------|
|  | SH   | Bright Silver           |
|  | MX   | Matte Nickel            |
|  | ABV  | Anodized Brushed Bronze |



\* Walk-Through

## Technical Information

All product dimensions are nominal.

Installation type: For receptor installation

Opening style: Pivot

Opening Width - Min: 30" (762 mm)

Opening Width - Max: 31-1/2" (800 mm)

Walk-through - Min: 24-1/4" (616 mm)

Walk-through - Max: 25-3/4" (654 mm)

Glass thickness: 1/4" (6 mm)

## Notes

Install this product according to the installation guide.