

# 117-160 **Alto**™

Round Front, SmartHeight™, Vitreous China, Two-Piece Toilet

### **Features**

- · Contemporary design
- SmartFlush™ siphon jet flushing technology with exclusive flapperless Mansfield® flush tower provides outstanding flushing performance
- 1.6 gpf / 6.0 lpf low water consumption
- Glazed trapway
- Anti-siphon ballcock
- 12" rough-in
- Large 8-9/16" x 9-3/8" water surface

tank liner.

- Available in White, Standard Colors: Biscuit, Classic Bone and Classic Silver
- Model 40 chrome plated, plastic trip lever (Consult Price Book for additional finishes)
- Outstanding protection The Mansfield® limited lifetime warranty



Model No.	Description	Approx. Wt.
117-160	Round front, SmartHeight™ (1.6 gpf/6.0 lpf) two-piece toilet. 12" rough-in. Includes tank trim and front-mount, chrome plated, plastic trip lever. Less toilet seat and supply. Specify color.	77 lbs. (35 kg)
117	Round front, SmartHeight™ toilet bowl only. 12" rough-in. Less toilet seat. Specify color.	46 lbs. (21 kg)
160	Tank and cover only, with left hand, front-mount, chrome plated, plastic trip lever. Less supply. Specify color.	31 lbs. (13.9 kg)
125	Same as model 160, with 14" rough-in.	33 lbs. (15 kg)
160RH	Same as model 160, with right hand trip lever.	31 lbs. (13.9 kg)
161	Same as model 160, with Fluidmaster™ 400A ballcock.	31 lbs. (13.9 kg)
165	Same as model 160, with cover lock.	31 lbs. (13.9 kg)
170	Same as model 160, with tank liner.	31 lbs. (13.9 kg)
171	Same as model 160, with Fluidmaster™ 400A ballcock and tank liner.	31 lbs. (13.9 kg)
175	Same as model 160, with cover lock and tank liner.	31 lbs. (13.9 kg)
180	Same as model 160, with color-match trip lever.	31 lbs. (13.9 kg)
181	Same as model 160, with Fluidmaster™ 400A ballcock and color-match trip lever.	31 lbs. (13.9 kg)
190	Same as model 160, with color-match trip lever and	31 lbs. (13.9 kg)





Smart**Height**™

# 117-160 **Alto**™

## Round Front, SmartHeight™, Vitreous China, Two-Piece Toilet

# Features & Upgrades

#### Three-Point Cushioned Tank-to-Bowl Connection

This assures perfect tank alignment in every direction. It permits fast, accurate, leakproof tank-to-bowl connections. Protects against tank breakage... can't be rocked loose... saves installation time. Furnished with nuts and bolts.

#### 211 Flush Valve

The 211 flush valve provides 1.6 gpf / 6.0 lpf water conservation efficiency with non-corrosive, long-life dependability. It seals tight every time. Won't rust or corrode.



#### 88 Anti-Siphon Ballcock

The 88 anti-siphon ballcock affords efficient toilet tank operation at high or low water pressures. Adjustment screw allows water level adjustment without bending the float rod. Completely non-electrolytic and non-corrosive.



## **Technical Information**

#### **Specifications**

Material Vitreous China
Water Pressure Range 20 to 80 P.S.I

Flush System SmartFlush™ Flushing

Technology

Water Usage 1.6 gpf / 6.0 lpf Water Surface Area 8-9/16" x 9-3/8"

Trap Diameter 1-7/8"

Trap Seal 2-7/8"

Rough-in 12"

Shipping Dimensions Model 117

25-3/8" x 14-7/8" x 16-7/8" (645 mm x 378 mm x 429 mm)

Model 160

19-3/4" x 10" x 14-3/4"

(502 mm x 254 mm x 375mm)

Shipping Weight Model 117 - 52 lbs (24 kg)


Model 160 - 34.1 lbs (15 kg)

Warranty Vitreous China - Limited Lifetime

Tank Trim - Limited One Year

These dimensions are nominal and are subject to change without prior notice.

Fixture performance and specifications meet or exceed, ANSI/ASME A112.19.2 standards and CAN/CSA B45.0 standards, and other state and local codes.



NOTE: Install this product according to the installation guide. Fixture dimensions are nominal and conform to tolerances in ASME Standard A112.19.2

See our complete line of acrylic and vitreous china bathroom fixtures, plastic tank trim and plumbing products.

