

Item #: **8202-61**
UPC Code: **747396041933**
Product Family Name: **Segovia™**
Finish: **Vintage Rust™**
Category: **Wall Mount**
Category Type: **Wall Bracket**
Certification: **E87611-ZSLRU**
Patents: **U.S. Patent(s): D510,453; D512,793; D518,224**
Notes:



Image File Name:
8202-61--
1377129148.jpg



MEASUREMENTS

Width:	Length:	Height:	Extension:
8.75		17	10.25
Height Adjustable:	Min Overall Height:	Max Overall Height:	Slope:
No			No
Wire Length:	Chain Length:	Safety Cable Included:	Net Weight
7		No	5.07
Canopy Width:	Canopy Height:	Canopy Length:	
5.25	7		
Backplate Width:	Backplate Height:	Center to Top:	Center to Bottom:
		2.75	14.25

LAMPING

No. of Bulbs:	Light Type:			
1	A19 Med			
Max Bulb Wattage:	Socket:			
100	E26 Med			
Dimmable:	Ballast:	Rated Life Hours:	Photocell Included:	Lamps Included:
Yes				No
Lamp Included:	Color Temp.:	CRI:	Initial Lumens:	Delivered Lumens:
No				



SHIPPING

Carton Width:	Carton Height:	Carton Length:	
10.75	17.5	12.25	
Carton Weight:	Carton Cubic Feet:	Small Package Shippable:	
6.93	1.334	Yes	
Master Pack Width:	Master Pack Height:	Master Pack Length:	
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:	Master Pack:
		1	1

SHADE / GLASS

Description:		Material:	
		Optic Glass	
Part No.:		Quantity:	
G8202		1	
Width:	Height:	Length:	



Wet Location

Yes



UL Listed

Yes