

Ammonium Sulfate 21-0-0 2 grades available: Soluble Fines and Standard Grade

DESCRIPTION: AN ECONOMICAL SOLUBLE FORM OF QUICK GREENING NITROGEN WITH HIGH SULFUR

BENEFITS: BEST® AMMONIUM SULFATE 21-0-0

- Is a quick acting form of water soluble nitrogen that stimulates vegetative growth and produces deep green color.
- Contains high sulfur (24%) to enhance decomposition of thatch through stimulation of soil micro-organisms, improves color and density of turf.
- Is a very economical form of nitrogen and sulfur.
- Is a very high quality, screened crystaline material that is not produced as a result of any bi-product manufacturing process.

APPLICATION RATES:

	Pounds of Actual	Pounds of BEST Ammonium Sulfate	Pounds of BEST Ammonium Sulfate	Lbs. of Actual
	Nitrogen desired per 1,000 sq.ft.	21-0-0 to apply per 1,000 sq.ft.	21-0-0 to apply per Acre	Sulfur Applied per 1,000 sq.ft.
Turfgrass:	0.50	2.3	100	0.55
9	0.75		155	0.84
Recommended Rate	1.00	4.7*	205*	1.13*

Application at the recommended rates will last approximately 4 to 6 weeks.

GROUNDCOVER: Broadcast at 5 lbs. per 1,000 sq.ft. (1/2 lbs. per 100 sq. ft.)

SHRUBS & EVERGREENS: Sprinkle 1/4 cup evenly around dripline of plant and work into top 1 inch of soil.

TREES: Apply ½ lb. per 1 inch of trunk diameter. Distribute evenly under branches out to dripline.

NOTE: Liquid measuring cups are very close in estimating the weight of dry granular fertilizers. Example: an 8 oz. (1 cup) measuring cup holds approximately 8 oz. of dry granular fertilizer.

PRODUCT COVERAGE:

Based on the Recommended Turfgrass Rate

ONE 50-LB. BAG COVERS 10,600 SQ.FT. 41/2- 50-LB. BAGS COVER 1 ACRE



Tech sheets, MSDS and other information on BEST products available at www.bestfertilizer.com

SPREADER SETTINGS:

Listed Settings Will BEST® Pro Rates are for spreading one Spyker / BEST[®] Models 34, 44, 64..... time across in one direction Approximately Apply the 48 Recommended Rate. Earthway..... Scotts R-8A (Cone 6).... Lely 1250 / Vicon visit www.bestfertilizer.com

SGN 150 NOTE: Spreader settings are guidelines only. Spreaders should be checked for accuracy.

APPLICATION PRECAUTIONS:

- Apply to dry turf or foliage and irrigate thoroughly immediately after application.
- Keep away from pools, ponds, etc. Do not contaminate potable water.

GUARANTEED ANALYSIS:

TOTAL NITROGEN (N)	
21.0%	Ammoniacal Nitrogen
Sulfur (S)	24.00%

Derived from Ammonium Sulfate

PACKAGE SIZE:

Information regarding the contents and levels of metals in this product is available on the Internet at http://www.regulatory-info-ir.com

50-LB. (22.68-Kg.) BAGS

HANDLING PRECAUTIONS:

MSDS: See Reverse

CAUTION: KEEP OUT OF REACH OF CHILDREN HARMFUL IF SWALLOWED — DO NOT INHALE

Spread The Word



74042BAG (PRO/TB R7-29-2011)