

Submittal Data Sheet

MODELS PF200SD-1/2"



PF200SF-3/4", PF200SG-1"

PF200SH-1 1/4" PF200SJ-1 1/2"

PF200SK-2", PF200SM-3", PF200SP-4"


BRONZE BALL VALVES

PRODUCT FEATURES

- Feature PTFE seats and stem seats
- 225 psi at min. -4° F, max. 300° F
- 400 psi WOG, ISO 9000
- Standard Port - 400#
- Sweat end


WARRANTY AND CODES

1-year limited warranty



PRODUCT SPECIFICATIONS

POS.	PART	MATERIALS
1	BODY	OT 58 brass UNI 5705/65
2	BODY END	OT 58 brass UNI 5705/65
3	SEATS	PTFE
5	STEM	OT 58 brass UNI 5705/65
6	STEM SEAT	PTFE
7	PACKING NUT	OT 58 brass UNI 5705/65
8	HANDLE	STEEL ZINC PLATED, PLASTIC COATED



D	1/2"	3/4"	1"	1 1/4"	1 1/2"	2"	2 1/2"	3"	4"
DN	11	15	20	25	32	40	50	61	74
P	14	20	25				60		
T	16,00	22,30	28,66	35,01	41,37	54,07	66,77	79,47	104,89
S	52	71	83	87	102	122	150	177	204
G	15	22	26				41		
F	13	19	23	25	28	34	38	46	53
H	41	44,5	57	61	71	76	92	108	115,5
L	80	92	115	115	125	150	140	200	200

TESTING PRESSURE

SHELL: 340 PSI (HYDRO)

SEAT: 100 PSI (AIR)

WORKING PRESSURE

400 PSI

WORKING TEMPERATURE

MIN.: -4° F

MAX.: +30° F