



Job Name:

Job Type:

Comments:

Quantity:

9456-12: 12v 60-150w Transformer Hardwire



Dimensions:

Length: 6 1/4"
Width: 2 1/4"
Height: 1 11/16"

Mounting Proc.: N/A

Material List:

1 Transformer - Plastic -
Black

Safety Listing:

UL Listed for Dry Locations
cUL Listed for Dry Locations

12V Transformer/Hardwire Electric Soft Start Curcuitry UL& C-UL
Approved W/ Terminal Block For Romax Input & 10/2 AWG Cable
Output

Electronic transformers have soft start circuitry which increases lamp
life. They emit no audible noise, are UL and C-UL approved, moisture
and shock resistant, employ automatically resetting short circuit
protection, and are dimmable.

Includes terminal block for 12/2 AWG max. romex input and 10/2
AWG Ambiance® cable output.

UPC #:785652945625

Finish: Black (12)

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	UPS Ship
Individual	9456-12	1	785652945625	6	3	3	0.031	0.9	Yes
Master Pack		2	10785652945622	6	6	6	0.125	1.95	Yes
Shipping Master		32	10785652945622	25.5	13	13.75	2.638	34.2	Yes
NJ Pallet		960		48	40	72	80	1026	No
NV Pallet		960		48	40	67	74.444	1026	No