
LS300W

Luminator sensor with 110° view, manual override, 300 watt switching capacity and auto test logic.

Color: White

Weight: 0.7 lbs



Technical Specifications

UL Listing:
Suitable for wet locations.

Voltage:
120 volts AC 60 Hz.

Power Consumption:
1 watt

Time Adjustment:
8 seconds to 10 minutes

Photo Control:
Deactivates lights during daylight

Detector Sensitivity:
Adjustable from 100% to 50%

Wall Switch Manual Override:
Two flip logic prevents activation by momentary power outages. Override resets to auto after 6 hours or at dawn. No extra wiring needed.

Auto Test Logic:
5 minutes of test time when power is turned on, Rests to auto mode without further adjustment

Sensor Housing:
Made of tough, corrosion resistant polycarbonate

Floodlights:
Made of tough, corrosion-resistant polycarbonate. Accepts PAR-38 lamps, medium base, 150 watts max. Lamps not included.

Surge Protection:
Withstands up to 3000 volts

Detection:
110° view

Switching Capacity:
300 watts incandescent @ 120 volts, 2.5 amps

Patents:
RAB sensor and fixture designs are protected under U.S. and International Intellectual Property laws.

Copyright ©2013 RAB Lighting, Inc. All Rights Reserved