


# WPTS70

HPS "Tall" Wallpack. Vandal resistant polycarbonate housing. Heavy die-cast aluminum back plate with 1/2" bottom and back conduit knockout. Factory installed 120V photocell with bypass cap included. Glare shield included. Lamp supplied.

Color: Bronze

Weight: 6.2 lbs



## Lamp Info

Type: ED17  
Watts: 70W  
Shape/Size: N/A  
Base: N/A  
ANSI: N/A  
Hours: 24,000  
Lamp Lumens: 6,300  
Efficacy: 73 LPW

## Ballast Info

Type: R-NPF 120V  
120V: 2.1/1.6  
208V: N/A  
240V: N/A  
277V: N/A  
Input Watts: 86W  
Efficiency: 81%

## Technical Specifications

### UL Listing:

Suitable for wet locations

### Reflector:

Die formed aluminum for wide light distribution.  
Moveable Glare Shield for field adjustable light control  
slanted slightly downward for more light on the job

### Ballast Housing:

Stamped steel painted white

### Back Plate:

Heavy die cast aluminum. 1/2" bottom conduit knockout.  
Knockouts for mounting to 3" or 4" junction boxes

### Housing and Refractor:

Vandal resistant polycarbonate molded refractor. Die cast aluminum back plate

### Patents:

The unique RAB Tallpack is protected by U.S. Patent D569,029; China Patent ZL200730149211.2; Taiwan Patent D124,864 and Canada Patent D121,993