

# QF500FW

Sleek design 500 watt Quartz flood with rounded back and fins for superior heat dissipation. Vandalproof stainless steel locking clip. Gold plated socket contacts and 250&deg;C Teflon coated wires for extended lamp life. Lamp supplied.

Color: White

Weight: 2.8 lbs



## Lamp Info

Type: T3  
Watts: 500W  
Shape/Size: N/A  
Base: N/A  
ANSI: N/A  
Hours: 2,000  
Lamp Lumens: 11,000  
Efficacy: 22 LPW

## Ballast Info

Type: 0  
120V: N/A  
208V: 0  
240V: N/A  
277V: N/A  
Input Watts: 500W  
Efficiency: 100%

## Technical Specifications

### UL Listing:

Suitable for wet locations. Suitable for mounting within 1.2m (4ft) of the ground

### Housing:

Die cast aluminum, 1/2" NPS threaded arm with locking swivel fits all standard mounting covers.

### Lens Gasket:

High temperature silicone gasket stays in place during relamping

### Reflector:

Semi-specular anodized aluminum

### Sockets:

Porcelain RSC base sockets with gold plated spring loaded contacts and strain relieved 250&deg; C Teflon insulated wires

### Lens:

Thermal, tempered, shock resistant glass

### Finish:

Chip and fade resistant polyester powder coating

### Patents:

RAB sensor and fixture designs are protected under U.S. and International Intellectual Property laws

: