STANDARD CHECK VALVES





Economy Check Valves

CV2N1 1-1/4" and 1-1/2" combo

CV150 1-1/2"

CV200 2"

- •ABS valve body
- •Rubber slip connect with hose clamps
- •Vertical or horizontal installation
- •15 PSI rated for CV2N1 and CV150
- •25 PSI rated at 140°F for CV200



Ball/Check/Union Combination

BCV150 1-1/2"

BCV200 2"

- •Ball/check combo provides compact design
- •Heavy-duty PVC
- •150 PSI rated at 72°F
- •Vertical or horizontal installation
- •Features union for easy disassembly
- Socket weld connections



Thread X Barb Fit

CV150-125T 1-1/2" MPT x 1-1/4" Barb

CV150-150T 1-1/2" MPT x 1-1/2" Barb

- PVC construction
- •Thread directly into 1-1/2" sump pump discharge
- •30 PSI rated



Heavy-Duty Compression Fit

CV2N1C 1-1/4" and 1-1/2" combo

CV200C 2" CV300C 3"

- •Heavy-duty PVC
- •Vertical or horizontal installation
- •150 PSI at 72°F for CV2N1C and CV200C
- •125 PSI at 72°F rated for CV300C





HCV150 1-1/2" HCV200 2"

- Heavy-duty cast-iron body
- •Full flow
- High-temperature rubber flapper - 200°F
- •125 PSI rated
- Vertical or horizontal installation
- •Female NPT connections

