

Zero Clearance Gas Fireplace
HBZDV3624/28, HBZDV4224/28

Direct Vent Gas Fireplace




The ultimate in design, engineering & quality

Model HBZDV3624/28, HBZDV4224/28 Specifications

Corner Framing Dimensions (inches)

Louvered		Clean View Circulating Kit (CVCK)	
HBZDV36	HBZDV42	HBZDV36	HBZDV42
A	54 ¹³ / ₁₆ "	59 ⁷ / ₈ "	63 ¹³ / ₁₆ "
B	36 ³ / ₈ "	38 ⁷ / ₁₆ "	42 ⁷ / ₁₆ "
C	36"	38 ¹ / ₁₆ "	42 ¹ / ₁₆ "
D	9 ³ / ₁₆ "	10 ¹¹ / ₁₆ "	10 ¹ / ₁₆ "
E	38 ³ / ₄ "	42 ⁵ / ₁₆ "	45 ¹ / ₈ "
F	12 ³ / ₈ "	12 ³ / ₈ "	13 ³ / ₄ "
G	17 ⁹ / ₁₆ "	17 ⁹ / ₁₆ "	19 ¹ / ₂ "
H	27 ³ / ₈ "	29 ¹⁵ / ₁₆ "	31 ⁷ / ₈ "



Top Flue Model	Height		Front Width		Depth	
	Actual	Framing	Actual	Framing	Actual	Framing
Louvered						
HBZDV36	34 ¹³ / ₁₆ "	35"	36"	36 ³ / ₈ "	16 ⁷ / ₁₆ "	17"
HBZDV42	37"	37 ¹ / ₈ "	41 ⁷ / ₈ "	42 ³ / ₈ "	16 ⁷ / ₁₆ "	17"
Clean View Circulating Kit (CVCK)						
HBZDV36	34 ¹¹ / ₁₆ "	41"	38 ¹ / ₁₆ "	38 ⁷ / ₁₆ "	18 ⁷ / ₈ "	19 ¹ / ₂ "
HBZDV42	36 ¹³ / ₁₆ "	43"	42 ¹ / ₁₆ "	42 ⁷ / ₁₆ "	18 ¹⁵ / ₁₆ "	19 ¹ / ₂ "

Top Flue Model	Width	Height
Viewing Area		
HBZDV36	29 ³ / ₄ "	18 ⁵ / ₈ "
HBZDV42	33 ³ / ₈ "	20 ³ / ₈ "

Model	HBZDV3624N	HBZDV3628N	HBZDV3624LP	HBZDV3628LP
	HBZDV4224N	HBZDV4228N	HBZDV4224LP	HBZDV4228LP
Flue	top	top	top	top
Fuel	natural	natural	propane	propane
Input Max.	24,000 BTU	28,000 BTU	22,000 BTU	26,000 BTU
Input Min.	14,000 BTU	20,000 BTU	15,000 BTU	19,000 BTU
Output Max.	-	21,000 BTU	15,000 BTU	19,500 BTU
Efficiency	-	76% fan on	-	76% fan on
FE (P4.1-02)	51.0%/44.7%	58.7%/57.7%	46.0%/47.9%	62.4%/58.6

Kingsman Industries maintains a program of continuous testing refinement and improvements of all its products. Some aspect of units shown here may be changed at any time without notice or obligation.

Certification: The Model HBZDV3624/4224 are certified to ANSI Z21.50a-2000/CSA 2.22a-2000, CCA 2.17-M91, CSA P4.1-02 vented gas fireplace.
The models HBZDV3628/4228 are certified to ANSI Z21.88b-2003/CSA-2.33b-2003, CAN/CGA 2.17-M91, CSA P4.1-02 vented gas fireplace heater.



Standard Features

- Millivolt valve system allows operation during a power failure with Hi/Low heat and flame adjustment
- Dual burner with Realistic Flame Pattern
- A flame sensor that constantly monitors the pilot flame and provides 100% gas shut off if pilot is not sensed

Optional Features

Designer Clean View Circulating Kit – (No Louvers Required), Optional Pull Screens

Decorative Black Panels or Grills – Grills available in Black, or Classic Series Black with Polish Brass, Antique or Chrome Accents

Overlay Doors – Deluxe, Top Half, Double Arch and Double Door

Designer Doors – Arch or Straight Black Doors with Antique, Polished or Chrome Trims

Surrounds Wide (Louvered Units) - Polish Brass, Antique or Chrome

Coverage – HBZDV3624/28 – 34¹/₂" h x 41¹/₈" w
HBZDV4224/28 – 36⁵/₈" h x 45¹/₈" w

Surrounds Slim Line (Louvered Units) - Polish Brass,

Antique Brass, Chrome or Gun Metal Black,
Coverage – HBZDV3624/28 – 34¹/₄" h x 37¹/₂" w
HBZDV4224/28 – 36³/₈" h x 43³/₈" w

Fan Kit – Heat activated with variable speed control

Brick Refractory Liner – Traditional or Herringbone

Thermostat – Wall Mount Millivolt Thermostat or Programmable Thermostat

Remote Control – On/Off, Thermostat On/Off, Hi/Lo On/Off

Child Safety Screen

Log Sets – Choose from our LOGC42 Classic Oak Four Piece or LOGC43 Traditional Oak Four Piece or LOGC44 Burnt Oak Eight Piece Log Sets



LOGC44 Log Set

Unit illustrated is a HBZDV3628N Zero Clearance Direct Vent Fireplace – Natural Gas, with LOGC44 Log Set, HB36CBL Grill Kit – Black, and Optional HB36RLH Herring Bone Refractory Liner, HB36ADDD Double Arch Door

This unit illustrated is a HBZDV4228N Zero Clearance Direct Vent Natural Gas Fireplace, with LOGC43 Log Set and optional HB42RLT Traditional Refractory Liner, and HB42DDAIBL Designer Arch Door.

