# TSW SERIES 1/3 HP

#### **APPLICATIONS**

• Basement sumps • Flood control

#### **FEATURES**

- Permanent split capacitor motor
- Designed to be installed suspended from basin cover
- Non-corrosive construction
- Integral IntelliPlug® provides high water alarm light and 85 dba alarm with run light built in
- Leg kit raises up 2-1/4" (5.7 cm) if not used in basin
- 1-1/2" FNPT (38 mm) discharge
- Side screened inlet
- 140 °F (60 °C) liquid temperature rating
- cCSAus listed



#### **SERIES SPECIFICATIONS**

Volts	Hz	Amps		Watts	Performance Watts (GPM @ Height in Feet)		Shut-Off	PSI	
		FLA	Start		5'	10'	15'	(ft)	
115	60	4.5	11.6	475	50	40	32	30	13.1

Item No.	Model	HP	Volts	Switch Type/ Operation	On Level	Off Level	Alarm Level	Cord	Weight
507700	TSW-SP	1/3	115	Integral Solid State Electronic	9.5" - 10.5" 24 cm - 27 cm	2.5" - 3.5" 6.4 cm - 9 cm	11" - 12" 28 cm - 30.5 cm	10' 3 m	17 lbs 7.71 Kg

## BATTERY BACK-UPS TSW-APS 1/3 HP

#### **APPLICATIONS**

Basement sumps • Flood control

#### **FEATURES**

- Eliminates need and cost of installing a "back-up" pump that operates when power is out.
- Converts pump to DC power in the event of a power failure
- Includes inverter, battery box, and battery cover strap (battery not included)



Item No.	Model
507701	TSW-APS

#### **SYSTEMS & COMPONENTS**

**TSW-A Series** - System includes: Pump, clear view cover, and discharge kit with clear check valve

507709, TSW-A22 (For use with 22" (56 cm) basin #507705, TSW-B1822A) 507710, TSW-A30 (For use with 30" (76 cm) basin #507707, TSW-B1830A)



**TSW-B Series** - System includes: Pump, 22" or 30" (56 cm or 76 cm) basin, clear view cover assembly, and discharge kit with clear check valve 507711, TSW-B22A [22" (56 cm) unit] 507713, TSW-B30A [30" (76 cm) unit]



**TSW-C Series** - System includes: Pump, clear view cover assembly, discharge kit with clear check valve, and Auxiliary Power System (TSW-APS) 507715, TSW-C22 [For use with 22" (56 cm) basin #507705, TSW-B1822A] 507716, TSW-C30 [For use with 30" (76 cm) basin #507707, TSW-B1830A]



**TSW-D Series** - System includes: Pump, 22" or 30" (56 cm or 76 cm) basin, clear view cover assembly, discharge kit with clear check valve, and Auxiliary Power System (TSW-APS)

Description

507717, TSW-D22A [22" (56 cm) unit] 507719, TSW-D30A [30" (76 cm) unit]



#### **Component Variations Available:**

Model

Item


507700 TSW-SP	TSW Sump Pump
507701 TSW-APS	Auxiliary Power System
507702 TSW-CVC	Clear View Basin Cover
507703 TSW-DPK22	Discharge Kit for 22" (56 cm) Deep Basin
507704 TSW-DPK30	Discharge Kit for 30" (76 cm) Deep Basin
507705 TSW-B1822A	18" x 22" (45.7 cm x 56 cm) Poly Basin with Adapt-A-Flex Inlet Fitting
507707 TSW-B1830A	18" x 30" (45.7 cm x 76 cm) Basin with Adapt-A-Flex Inlet Fitting
507721 TSW-SP-C	TSW Sump Pump and Auxiliary Power Supply


Hotline: 1.800.701.7894 www.franklinwater.com


TSW SERIES 1/3 HP

## **ENGINEERING DATA**

#### **PUMP DIMENSIONS**








Overall dimensions without leg kit

Overall dimensions with leg kit


	A	В	C	D
W/O Leg Kit	10"	11.8"	9.3"	8.12"
	25.4 cm	29.97 cm	23.62 cm	20.62 cm
W/ Leg Kit	13"	18.3"	9.3"	8.12"
	33.02 cm	46.48 cm	23.62 cm	20.62 cm

#### **BASIN DIMENSIONS**



	A	В	C
22"	22"	15"	21"
56 cm	56 cm	38 cm	53 cm
30"	30"	15"	-
76 cm	76 cm	38 cm	

## PERFORMANCE DATA



## CONSTRUCTION

Motor Housing	Engineered thermoplastic		
Impeller Material	Engineered thermoplastic		
Impeller Type	Vortex		
Volute	Engineered thermoplastic		
Motor Shaft	Stainless steel		
Shaft Seal	Mechanical nitrile with carbon ceramic faces		
Fasteners	Stainless steel		
Bearings	Upper and lower ball bearings		
Power Cord	SJTW-16		

## **BASIN CONSTRUCTION**

Clear View Basin Cover	ABS		
Basin	Polypropylene		
Basin Capacity (approx.)	22" (56 cm) basin – 22 gallons 30" (76 cm) basin – 30 gallons		
Discharge Size	1-1/2" (38 mm)		
Intake Size	4" Adapt-A-Flex**		

<sup>\*\* 4&</sup>quot; hub available as an option