



**Undertone®**  
Under-mount Kitchen Sink  
**K-3177-L**

**Features**

- 36-inch minimum base cabinet width.
- 18-gauge stainless steel.
- Under-mount.
- Double (large/medium) compartment.
- Squared bowl(s).
- 7-1/2" (191 mm) deep left bowl and 9-1/2" (241 mm) deep right bowl.
- With SilentShield® sound-absorption technology.
- 31-1/2" (800 mm) x 20-7/8" (530 mm)

**Optional Accessories**

- K- 3190 Sink Rack
- K- 3277 Sink Basket
- K- 3294 Cutting Board
- K- 6139 Sponge Caddy
- K- 8801 Sink Strainer

**Components**

Product includes:  
91915 Hardware Kit




**Codes/Standards**

ASME A112.19.3/CSA B45.4

**Lifetime Limited Warranty for  
KOHLER® Stainless Steel Sinks**

See website for detailed warranty information.



### Technical Information

All product dimensions are nominal.

Bowl configuration: Large/medium

Installation: Under-mount

Bowl area (Right) Length: 14" (356 mm)  
Width: 19" (483 mm)  
Bowl depth: 9-1/2" (241 mm)

Bowl area (Left) Length: 14" (356 mm)  
Width: 16" (406 mm)  
Bowl depth: 7-1/2" (191 mm)

Drain hole: 3-5/8" (92 mm)

Template: Under-mount, 1040557-7, required,  
included

### Notes

Install this product according to the installation guide.

Allow a minimum of 2" (51 mm) clearance around the sink rim for clip attachment.