



Undertone®
Under-mount Kitchen Sink
K-3177

Features

- 36-inch minimum base cabinet width.
- 18-gauge stainless steel.
- Under-mount.
- Double (large/medium) compartment.
- Squared bowl(s).
- 9-1/2" (241 mm) deep left bowl and 7-1/2" (191 mm) deep right bowl.
- With SilentShield® sound-absorption technology.
- 31-1/2" (800 mm) x 20-7/8" (530 mm)



Optional Accessories

- K- 3190 Sink Rack
- K- 3277 Sink Basket
- K- 3294 Cutting Board
- K- 6139 Sponge Caddy
- K- 8801 Sink Strainer

Components


- Product includes:
91915 Hardware Kit

Codes/Standards

ASME A112.19.3/CSA B45.4

**Lifetime Limited Warranty for
KOHLER® Stainless Steel Sinks**

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Bowl configuration:	Large/medium
Installation:	Under-mount
Bowl area (Left)	Length: 14" (356 mm) Width: 19" (483 mm) Bowl depth: 9-1/2" (241 mm)
Bowl area (Right)	Length: 14" (356 mm) Width: 16" (406 mm) Bowl depth: 7-1/2" (191 mm)
Drain hole:	3-5/8" (92 mm)
Template:	Under-mount, 1040557-7, required, included

Notes

Install this product according to the installation guide.

Allow a minimum of 2" (51 mm) clearance around the sink rim for clip attachment.