



**Undertone®**  
Under-mount Kitchen Sink  
**K-3166**

**Features**

- 45-inch minimum base cabinet width.
- 18-gauge stainless steel.
- Under-mount.
- Rounded bowls.
- Triple compartment.
- 9-1/2" (241 mm) deep left bowl, 7-1/2" (191 mm) deep right bowl and 5-1/2" (140 mm) deep center bowl.
- With SilentShield® sound-absorption technology.
- 41-5/8" (1057 mm) x 20-1/8" (511 mm)

**Optional Accessories**

- K- 3278 Cutting Board
- K- 3291 Colander
- K- 6139 Sponge Caddy

**Components**

- Product includes:
- 91915 Hardware Kit




**Codes/Standards**

ASME A112.19.3/CSA B45.4

**Lifetime Limited Warranty for  
KOHLER® Stainless Steel Sinks**

See website for detailed warranty information.



## Technical Information

All product dimensions are nominal.

Bowl configuration: Two equal bowls and center bowl

Installation: Under-mount

Bowl area (Left) Length: 14" (356 mm)  
Width: 18" (457 mm)  
Bowl depth: 9-1/2" (241 mm)

Bowl area (Center) Length: 9" (229 mm)  
Width: 15" (381 mm)  
Bowl depth: 5-1/2" (140 mm)

Bowl area (Right) Length: 14" (356 mm)  
Width: 18" (457 mm)  
Bowl depth: 7-1/2" (191 mm)

Drain hole: 3-5/8" (92 mm)

Template: Under-mount, 1047579-7, required, included

## Notes

Install this product according to the installation guide.

Allow a minimum of 2" (51 mm) clearance around the sink rim for clip attachment.