

PART NUMBERS

304152	1 Case w/ (25) 11 oz. Cartridges (White)
304153	1 Case w/ (4) 1-Gallon Pails (White)
304155	1 - 2-Gallon Pail (White)

TECHNICAL DATA

Color	White
Consistency	Heavy textured
Base	Synthetic latex
Solvent	Water
Weight per Gallon	11.6 lbs.
Solids Content	73.4%
Viscosity	Thixotropic
Coverage (UL 181 A-M)	Apply 18 mil, scrim, addt. 18 mil
Coverage (UL 181 B-M)	Approximately 214 to 320 lin. ft. per gal. at 20 to 30 mil wet film thickness at 3" width
Shore A Hardness	>20
Flexibility	Passes ¼ inch mandrel bend
Time to Test	48 hours*
Service Temperature	-20°F to 200°F
Mildew Resistance	Mold & Mildew resistant
VOC	Exempt: 0 g/l Non-Exempt: 38 g/l (less water)
Surface Burning	Flame Spread - 0 Smoke Developed - 0 (When tested in accordance with ASTM E84, UL 723)
Pressure Classes	SMACNA ½ , 1, 2, 3, 4, 6 and 10 inches w.g.
Seal Class	Meets Seal Class A
Packaging	1 & 2 gal. pails; 10.3 oz. cart.
Freeze/Thaw Stability	Passed 5 Cycles

*May vary according to temperature and humidity

SPECIFICATION/STANDARDS COMPLIANCE

Property	Method	Results
Freeze Thaw & Heat Cycling	ASTM C-731	Pass
Slump Test	ASTM D-2202	Pass
VOC Limitation	SCAQMD Rule 1168	Pass
Acceptable Indoor Air Concentrations	Michigan Department of Quality Criteria (Part 201/213)	Pass
	US EPA	Pass
	NSF/AWSI Standard 61	Pass
	USDA	Pass
	FDA	Pass

Versa-Grip 102 is a general purpose, water based duct sealant for use on all types of metal duct, glass fiber duct board, and flex duct, as well as duct fabric and flexible tubing runouts. Versa-Grip incorporates a built-in fiber reinforcement for added strength, with UV inhibitors for extended outdoor exposure. UL 181A-M listed / UL 181B-M listed.

APPLICATION

Temperature	35°F to 110°F (1.7°C to 44°C)
Method	Brush, putty knife, caulk gun, pump
Preparation	Surface must be dry, dirt, oil, and grease free.
Rate (UL 181 A-M)	Apply 18 mil, scrim and 18 mil over scrim.
Rate (UL 181 B-M)	Approx. 214 to 320 lin. ft. per gal. at 20 to 30 mil wet film thickness at 3" width.
Clean Up Wet	Soap and water
Clean Up Dry	UN-TACK™ or Solvent (Use safe handling practices.)
Painting	Only latex or epoxy paints
Ductboard	Scrim required for UL 181A-M

STORAGE

Temperature	35°F to 110°F (1.7°C to 44°C) DO NOT FREEZE
Shelf Life	One year (unopened)
Flammability	Non-flammable

PRECAUTIONS

Surface must be clean and free of moisture, contamination and foreign matter. Do not allow this product to freeze. Apply when temperatures will not fall below freezing for at least 36–48 hours, depending on temperature and humidity. Do not apply this product where temperatures will exceed 200°F. Keep out of the reach of children. Review MSDS for complete safety information prior to use. DO NOT use where acidic or alkaline chemicals are present (ie., lab fume hood, vents, etc.)

For Industrial Professional Use Only.

Underwriters Laboratories Inc.®
LISTED
17NF
UL 181A-M
FOR USE WITH U.L. LISTED RIGID FIBERGLASS AIR DUCTS OR CONNECTORS.
UL 181B-M
FOR USE WITH U.L. LISTED FLEXIBLE AIR DUCTS OR CONNECTORS

City of Los Angeles Approval RR#8427

USDA, EPA & FDA
APPROVED

