


DOWNSPOUT NOZZEL



3940

CAST BRONZE DOWNSPOUT NOZZEL WITH THREADED OUTLET,
AND ANCHOR FLANGE



(INCHES)					
PIPE SIZE	A	C	D	E	G
2	5 1/4	7 5/8	1 7/8	5 5/8	8 1/4
3	5 1/4	7 5/8	1 7/8	5 5/8	8 1/4
4	5 1/4	7 5/8	1 7/8	5 5/8	8 1/4
5	5 7/8	7 3/4	1	5 7/8	8 1/2
6	7	8 3/4	1	5 3/4	9 1/2
8	9 5/16	10 7/8	1 1/8	5 3/4	11 5/8
10	11 7/8	12 7/8	1 3/4	6 1/8	14

(MILLIMETERS)					
PIPE SIZE	A	C	D	E	G
50	133.3	193.6	73.0	142.8	209.5
75	133.3	193.6	73.0	142.8	209.5
100	133.3	193.6	73.0	142.8	209.5
125	149.2	196.8	25.4	149.2	215.9
150	177.8	222.2	25.4	146.0	241.3
200	236.5	276.2	28.5	146.0	295.2
250	301.6	327.0	44.4	155.5	355.6

Cat. No.	Pipe Size	Wt. Lbs.
☐ 3942	2 (50)	10.5
☐ 3943	3 (75)	9.5
☐ 3944	4 (100)	9.5
☐ 3945	5 (125)	11.5
☐ 3946	6 (150)	13.5
☐ 3948	8 (200)	15.5
☐ 3949	10 (250)	19.5

OPTIONS

Suffix	Description
☐ 1	NICKEL PLATED BODY & FLANGE
☐ 2	SATIN FINISH ON BODY & ANCHOR FLANGE
☐ 85	S/S PERFORATED BIRD SCREEN
☐ 103	CHROME PLATED BODY & FLANGE

AutoCad.dwg