PFX146

Stainless Steel Water Heater

Reinforced Flexible Connectors

Product Features

- Working Temperature: 40°F to 140°F
- · Working Pressure: up to 125 PSI maximum
- Internal Hose: EPDM rubber
- Outer Wire Braid: 304 stainless steel
- Barb: low lead brass alloy
- Metal Nuts: nickel-plated brass alloy
- Ferrule: nickel-plated brass alloy
- Washer: EPDM rubber

Installation Instructions

- · For use with water in accessible locations only
- Metal Nuts: hand tighten plus 1/4 turn with wrench
- · Do not over tighten nuts
- Check for leaks before leaving job site
- Inspect regularly for general fitness and replace if damaged, corroded or worn
- Do not expose to corrosive chemicals

Models and Product (Certifications
----------------------	----------------

Model #	Description	cUPC	UPC	Low Lead Compliant
PFX146222	3/4" FIP X 3/4" FIP X 18" SS Water Heater	\checkmark	\checkmark	\checkmark
PFX146224	3/4" FIP X 3/4" FIP X 24" SS Water Heater	\checkmark	\checkmark	\checkmark
PFX146232	3/4" MIP X 3/4" FIP X 18" SS Water Heater	\checkmark	\checkmark	\checkmark

Warranty and Listing Certification This PROFLO product carries a 1-year limited warranty. IAPMO listed to ASME A112.18.6-2009 and CSA B125.6-2009 IAPMO listed to NSF/ANSI 372





PFX146224

