Hanger Rod or Pipe Not Included

B3199R - Ceiling Flange B3199RCT - Ceiling Flange Dura-Copper Coated

Size Range: 3/8"-16 & 1/2"-13 rod

Material: Malleable Iron (Stainless Steel Type 304 available)

Standard Finish: Plain or Electro-Galvanized B3199RCT is DURA-COPPER™ coated

Function: Designed for attaching a hanger or support rod to

beams, ceilings, or walls.

B3199R-3/8

B3199R-1/2

Order By: Part number and finish.


Part No.



Thread Size

3/8"-16

1/2"-13



17 (7.7)

(2 Holes)



180

| D313311 | | |
|---------|--------------------------|------------------------------|
| (mm) | Design Load Lbs. (kN) | Approx. Wt./100 Lbs. (kg) |
| (11.1) | 180 (.80) | 13 (5.9) |

(.80)

TOLCO™ Fig. 78 - All Steel Ceiling Plate

Size Range: 3/8"-16 rod **Material:** Pre-Galvanized Steel

Function: Attachment to wood beams, ceilings, metal decks

B3199RCT-3/8

B3199RCT-1/2

or walls. Can also be welded to steel beams.

Approvals: Underwriters Laboratories Listed in the USA (UL) and Canada (cUL). Additionally, UL has listed the Fig. 78 with

fasteners as shown in the table below.

Finish: Plain. Contact customer service for alternative

finishes and materials.

Order By: Part number, rod size and finish

US Patent #5,702,077



В

1/2" (12.7)

in.

7/16"

