



**COLEMAN CATALOG NUMBER:** See table below

**DESCRIPTION:** 16/3 SJTW outdoor use power supply cord with straight attachment plug cap.

**APPROVALS:** UL Listed (UL 817)

**CONSTRUCTION PARAMETERS:**

Conductor:	16 AWG, 26/30 bunched bare copper
Conductor O.D. (nom):	0.060"
Insulated conductor O.D. (nom):	0.120"
Insulation material:	PVC
Insulation colors:	Black White Green
Overall cable O.D. (nom):	0.330"
Jacket material:	PVC, black
Attachment plug configuration:	NEMA 5-15P
Plug material:	PVC, black
Open end configuration:	1.5" ROJ, 0.38" strip

**ELECTRICAL PROPERTIES:**

Temperature rating:	-35 to +60 °C
Maximum operating voltage:	125 VAC
Maximum operating current:	13 A
Maximum operating wattage:	1625 W

**PART NUMBERS**

Catalog number	Cable length
09703	3 ft
09706	6 ft
09709	9 ft

The information presented here is, to the best of our knowledge, true and accurate. However, since conditions of use are beyond our control, all recommendations or suggestions are presented without guarantee or responsibility on our part. We disclaim all liability in connection with the use of information contained herein or otherwise.

This specification is proprietary intellectual property of Coleman Cable Inc. Any information contained herein shall not be disclosed to any party without written consent of Coleman Cable Inc..

**CUSTOMER APPROVAL:** Approved by: \_\_\_\_\_ Date: \_\_\_\_\_  
 Title: \_\_\_\_\_