
Interior: 36 x 36 x 75 Exterior: 38 x 38 ½ x 77

The 1363BFSC transfer shower features innovative installation design, including an engineered leveled base and improved front threshold. A true time and money saver, our pre-leveled base lets you install directly on a **level** floor. And its front threshold is engineered to keep a constant level without the use of brackets during installation.



AQUATIC ADVANTAGE

- National distribution
- 6 manufacturing facilities
- Private fleet
- Centralized customer service
- Field support

COLOR & TRIM OPTIONS

| Stock | Upgraded |
|-------|---------------------------|
| White | Almond Biscuit Bone |

^{**}Additional custom colors available. (Contact Customer Service)

FEATURES

- Pre-leveled base
- AcrylX[™] applied acrylic surface
- 3/4" skirt
- No threshold
- Barrier free when properly installed
- Smooth wall
- Center drain
- Lifetime limited warranty (30 year commercial)

OPTIONS

- RH or LH fixture wall
- Grab bars
- Fold-up seat
- Hand-held shower assembly with slide bar
- Pressure balancing mixing valve
- Soap dish
- Curtain rod and/ or shower curtain

CODE COMPLIANCE

- ADA
- TAS
- FHA
- ICC/ANSI A117.1
- HUD UM73a
- IAPMO Z124-2011
- CAN/CSA-B651-04
- CSA-B45-11
 - **Code compliant when fully equipped and installed according to guidelines.



Aquatic products may be specified as Lasco Bathware.





Aquatic products may be specified as Lasco Bathware.

10"


1363BFSC


Interior: $36 \times 36 \times 75$ Exterior: $38 \times 38 \frac{1}{4} \times 77$ inches






TAS/ADA/ANSI compliant when fully equipped and installed according to guidelines.







FEATURES

Dimensional Tolerance ± %". Dimensions needed for site preparation should be measured from the unit. Aquatic assumes no responsibility for preparatory work

 Type and Model #
 Material
 Wall Finish
 Pieces
 Drain
 Dam/Skirt Height
 Net Wt. lbs
 Pkg. Wt. lbs

 Shower #1363BFSC
 AcryIX™
 Smooth
 1
 Center
 ¾" skirt, NO threshold
 140
 150

DIMENSIONS

| Specifications | inches |
|---------------------------------|-------------|
| Width: Overall / Net | 38 / 36 |
| Depth: Overall / Net | 38 1/4 / 36 |
| Height: Overall / Net | 77 / 75 |
| Enclosure Opening: | 36 |
| Skirt Height: | 3/4 |
| Drain Rough-In (from Back Wall) | 19 |
| Drain Rough-In (from Side Wall) | 19 |

FRAMING DIMENSIONS inches

| Туре | D Depth | W Width | H Height | А | В | С |
|--------|-------------------|-------------------|-------------|---------|----|----|
| Alcove | 38 1/4 | 38 1⁄8 | - | Box Out | 19 | 19 |

