
## **Architectural/Engineering Specification:**

Exposed, quiet piston type, chrome plated flushometer valve with a polished exterior. Complete with Zurn's MetroVantage chloramine resistant filtered by-pass. The valve is ADA compliant with a non-hold open and no leak handle feature. Internal seals are made of chloramine resistant materials.

#### **Product Features:**

- · Proprietary Dezincification resistant low lead brass alloy
- · Control Stop has internal siphon-guard protection, Sweat solder kit, wall flange with set screw.
- · High back pressure Vacuum Breaker with one piece hex coupling nut
- · Chloramine resistant Internal seals
- · Adjustable tailpiece
- · Spud coupling and flange for top spud connection





## Flow Options:

	Flush Volume	WaterSense Compliant
-HET	1.28 gpf	<b>✓</b>
-WS1	1.6 gpf	
-Standard	3.5 gpf	

## Suf

ffix Options:		
-BG	BioCare Handle	
-DF	Dual Flush Handle (See Chart Above)	
-L	1" [25] Metal Push Button	
-VC	Vandal Resistant Stop Cover	
-YJ	Split Ring Pipe Support	
-YK	Solid Ring Pipe Support	

### Rough-in/Overview dimensions

# Valve Height Options:

Product No.	Α
Z6200	11 1/2" [292]
Z6200-1	16" [406]
Z6200-2	24" [610]
Z6200-3	27" [686]

# **Compliance and Certification:**

- ADA Compliant
- WaterSense Compliant



Architectural/Engineering Approval

The information contained in this document is subject to change without notice. Please contact Zurn for most up to date information.

This product should be used with a WaterSense labeled counterpart with a compatible flow volume to ensure that the entire system meets the requirements for water efficiency and performance.