TWISTED PVC SUBMERSIBLE PUMP CABLE





FEATURES

- Operating temperature range -40° C to 75° C
- Resistant to acid, abrasion, alkalis, flame, gas, and oil
- Water resistant
- Special packaging is available upon request

APPLICATIONS

 For wiring within the casing of deep well submersible water pumps

CONSTRUCTION

Annealed bare solid or stranded copper conductors insulated with PVC and twisted to form a 75°C 600 Volt Multi-Conductor Submersible Pump Cable. UL Listed per UL 83 Type THW as Deep Well Submersible Pump Cable.







TWISTED PVC SUBMERSIBLE **PUMP CABLE**



GAUGE	STRANDING	INSULATION THICKNESS		TWISTED NOMINAL O.D.		STANDARD PACKAGE	SHIPPING WEIGHT ~lbs/
		in	mm	in	mm		1000 ft
14/2 with GND	Solid/.0641"	0.045	1.143	0.339	8.611	500 or 1000	67
14/3 with GND	Solid/.0641"	0.045	1.143	0.380	9.652	500 or 1000	89
12/2 with GND	Solid/.0808"	0.045	1.143	0.369	9.373	500 or 1000	94
12/3 with GND	Solid/.0808"	0.045	1.143	0.414	10.516	500 or 1000	125
10/2 with GND	Solid/.1019"	0.045	1.143	0.421	10.693	500 or 1000	136
10/3 with GND	Solid/.1019"	0.045	1.143	0.472	11.989	500 or 1000	182
8/2 with #10 GND	19/.0295" – solid (.1019")	0.060	1.524	0.538	13.665	500 or 1000	197
8/3 with #10 GND	19/.0295″ – solid (.1019″)	0.060	1.524	0.608	15.443	500 or 1000	273
6/3 with #8 GND	19/.0372" – 19/.0295"	0.060	1.524	0.728	18.491	500 or 1000	413
4/3 with #8 GND	19/.0469" – 19/.0295"	0.060	1.524	0.819	20.803	500 or 1000	584