

Coralais® Kitchen Sink Faucet K-15172-PT

Features

- Metal construction.
- One-piece, self-contained ceramic disc valve allows both volume and temperature control.
- Temperature memory allows faucet to be turned on and off at any temperature setting.
- Matching finish sidespray.
- Ground joint connections.
- 10" (254 mm) swing spout reach.
- Lower flow aerator options are available (refer to the Kohler Price Book).
- 1.8 gal/min (6.8 l/min) maximum flow rate [max at 60 psi (4.14 bar)].



1030920 Side Spray Deep Rough-In



ADA OBC

Codes/Standards

ASME A112.18.1/CSA B125.1 NSF 61 NSF 372 DOE - Energy Policy Act 1992 ADA ICC/ANSI A117.1 OBC

All applicable US Federal and State material regulations

KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.

Available Color/Finishes

Color tiles intended for reference only.

Color Code Description




CP Polished Chrome





Coralais® Kitchen Sink Faucet K-15172-PT



Technical Information

All product dimensions are nominal. Spout reach: 10" (254 mm)

Faucet:

Flow rate: 1.8 gal/min (6.8 l/min)

Pressure: 60 psi (4.1 bar)

Notes

Install this product according to the installation guide.

ADA, OBC compliant when installed to the specific requirements of these regulations.

