

Service Sink Faucets/ Mop Sink Faucets


TAG:	


B-0655-BSTR

Service Sink Faucet

Architect/Engineering Specifications:

8" wall mount mixing faucet with rough chrome plated brass body, rough chrome plated brass spout with vacuum breaker, pail hook and garden hose male outlet, compression cartridges with spring checks, lever handles, 1/2" NPT female extension inlets, built-in service stops in body, and lower support rod. Certified to ASME A112.18.1/CSA B125.1, NSF 61-Section 9, NSF 372 and ASSE 1001. Meets ADA ANSI/ICC A117.1 requirements.





Features & Benefits:

- 8" wall mount mixing faucet with rough chrome plated brass body
- Spout with vacuum breaker, pail hook & 3/4" garden hose male outlet
- · Lever handles with color coded indexes
- Quarter-turn Eterna compression cartridges with spring checks to prevent cross flow of water
- 1/2" NPT female eccentric extension inlets with Ø 2" flanges & 4" extensions
- Adjustable centers from 7 3/4" to 8 1/4"
- Built-in service stops in body
- · Lower support rod
- Material: Rough chrome plated brass body & spout and chrome plated metal handles

Product Compliance:

- ASME A112.18.1 / CSA B125.1
- NSF 61 Section 9
- NSF 372 (Low Lead Content)
- ANSI A117.1 (ADA)
- ASSE 1001 (VB)

Warranty: One Year (Limited)

Performance Data:

Pressure: 20 - 125 psi
Temperature: 40 °F - 140 °F

• Flow Rate: 12.96 GPM @ 60 psi









Optional Handles

- □ 4" Wrist Action
- ☐ Lever (Standard)
- □ 4-Arm

Optional Cartridges With Checks

- □ Quarter-Turn Cerama w/ Check Valve
- □ Quarter-Turn Eterna w/ Spring Check (Standard)







T&S BRASS AND BRONZE WORKS, INC.

