# UNIVERSAL BRACKETING SYSTEM

### 570 & 572 series

Pipe Titan<sup>™</sup>

#### **SPECIFICATION**

Sioux Chief 570 series Pipe Titan<sup>TM</sup> shall be used where necessary for bracketing applications. Bracket shall allow fastening on top or bottom edge. Molded pipe cradles shall be 1" on-center for quick and easy pipe alignment. Bracket shall have pilot holes for screws and slots for stainless steel bands. Bracket shall have holes on each end for 3%" thread rod for trapeze applications. Bracket shall prevent electrolysis and reduce transmission of waterline noise and vibration. Bracket and clamps shall be CPVC compatible. Bracket shall fit inside a 2 × 4 wall when fastened to 2" pipe. Bracket shall be UPC listed.

## **MATERIALS**

red bracket: fire-retardant ABS (UL-94 VO flame rating), U.V. stabilized green bracket: ABS, U.V. stabilized

red clamps: fire-retardant ABS (UL-94 VO flame rating), U.V. stabilized

white clamps: high-density polyethylene, U.V. stabilized

clamp screw: zinc-plated steel, 5/16" hex/Phillips

steel band: 300 stainless steel

band screw: 410 stainless steel, slotted/hex-head

#### **SAFE WORKING LOAD\***

mounting point 1 2 3 4 5 6 7 8 9 one end: 275 155 90 72 62 50 47 42 40 lbs.

balanced load: 190 lbs. total

stainless steel band: 60 in/lbs. ultimate torque

#### **DIMENSIONS**

A: Overall length 11"
B: Base height 2½"

C: Cradle centers 1" on-center

D: Bracket width  $1\frac{1}{4}$ "
E: Base width  $1\frac{5}{8}$ "
F: End holes  $1\frac{3}{32}$ "
G: stainless steel band slots  $9\frac{1}{14}$ "
H: Clamp height  $1\frac{1}{4}$ "
I: Clamp capacity  $5\frac{1}{8}$ "-1" O.D.


J: Strap height 7/8"

K: Strap capacity  $\frac{7}{8}$ " –  $3\frac{1}{2}$ " O.D.


L: Waste arm radius 13/4"


M: Pilot holes for clamp screws N: Stainless steel band  $\frac{1}{2}$ " wide × 0.025" thick

5" or 7" max diameter











Create Item Number

57A-B

e.g. 572-20 = Red bracket with two straps, one clamp, and one 5" stainless steel band.

A BRACKET

0 green

□ 2 red (fire-retardant)

**B** BRACKET CONFIGURATION

□ 10 two straps, one clamp \*

□ 20 two straps, one clamp, one 5"

stainless steel band

**B** BRACKET CONFIGURATION

□ 22 two straps, one clamp, one 5" stainless steel snap-lock band

□ 24 two straps, one 7" stainless steel snap-lock band

\* Only available with green bracket



<sup>\*</sup> One-half failure load at 72°F.