## K-3800 Drum Machine

Model K-3800









## For 3/4" to 4" (19-100mm) Drain Lines

## **Features**

A powerful, easy to transport, versatile machine for cleaning indoor drains. Requires minimal setup to clean sink lines, floor drains and roof vents.

Rugged, corrosion-resistant molded cable drum won't dent or rust. The drum tilt adjusts for proper cable feed angle. Inner-drum guards against cable flip-over.

Cable drum's quick-release and built-in handholds allow easy cable change and transport.

Standard drum capacity is 100' of 3/8" or 90' of 1/2" (30m/10mm or 27m/12mm) continuous length cable:

- -3/8" cable best for 1 1/2" to 3" lines up to 100'.
- 1/2" cable best for 2" to 4" lines up to 90'.

Optional sink drum holds up to 50' of 5/16" or 1/4" (15m/8mm) cable.

- Ideal for cleaning through 3/4" to 1 1/2" sink traps.

Powerful 1/12 HP Universal Motor spins cable at 240 RPM. When cable hits blockage, motor gears down automatically to deliver more power and enhance operator control.

Tools connect to cable in seconds.

CSA approved.

Approved to UL standards (NRTLC).

IW (Integral Wound) cables available. IW cables are slightly stiffer and kink resistant. All IW cables use 3/8" T-200 series cutters.



