

# SUBMITTAL FOR CHARLOTTE PIPE® SERVICE CAST IRON SOIL PIPE AND FITTINGS

Date: \_\_\_\_\_

Job Name: \_\_\_\_\_

Engineer:

Location: \_\_\_\_\_

Contractor:\_\_\_\_\_

## Scope:

This specification covers Service Cast Iron pipe, fittings, and compression gaskets used in sanitary drain, waste and vent (DWV), sewer, and storm drainage applications. This system is intended for use in non-pressure applications.

## Specification:

Pipe and fittings shall comply with ASTM A 74. Compression gaskets shall comply with ASTM C 564. All pipe and fitting shall be made in the United States, and marked with the collective trademark of the Cast Iron Soil Pipe Institute, . Service cast iron pipe and fittings are listed by NSF<sup>®</sup> International to the UP Code.


## Installation:

Installation shall comply with the latest installation instructions published by Charlotte Pipe and Foundry Company<sup>®</sup> and shall conform to all applicable plumbing, fire, and building code requirements. The system shall be hydrostatically tested after installation to 10 ft. of head (4.3 psi maximum). **WARNING!** Never test with or transport/store compressed air or gas in Cast Iron pipe or fittings. Doing so can result in explosive failures and cause severe injury or death.

## Referenced Standards:

ASTM A 74: Cast Iron Soil Pipe and Fittings

ASTM C 564: Rubber Gaskets for Cast Iron Soil Pipe and Fittings



Charlotte Pipe and Foundry Company • P.O. Box 35430 Charlotte, NC 28235 • (800) 438-6091 • www.charlottepipe.com


Charlotte Pipe and Charlotte Pipe and Foundry Company are registered trademarks of Charlotte Pipe and Foundry Company. FO-SUB-CI-SV (10-14-15)

#### PART NO. SV 170

Size	e X	C	J	Weight	T>
4	17½	6	6 <sup>1</sup> /2	19.3	
6	21½	8	8 <sup>1</sup> /2	48.0	<u>+                                    </u>
-					


#### PART NO. SV 174

Running Trap with Single Hub Vent							
Size	Vent Size	с	J	х	X'	Weight	
3	3	5	51/2	15	21/2	15.3	
4	4	6	6 <sup>1</sup> /2	17½	3	28.3	
5	4	7	7 <sup>1</sup> /2	19½	31/2	39.7	
6	4	8	8½	211/2	4	45.9	
8	4	10	11	275/8	5 <sup>1</sup> /4	95.9	
8	6	10	11	27 <sup>5</sup> /8	5 <sup>1</sup> /4	110.0	



#### PART NO. SV 175

Running Trap with Double Hub Vent							
Size	Vent Size	с	J	х	X'	Weight	
3	3	5	51/2	15	21/2	23.0	
4	4	6	6 <sup>1</sup> /2	17½	3	36.3	
5	4	7	71/2	191/2	31/2	42.5	
6	4	8	81/2	21½	4	57.3	
6	6	8	8 <sup>1</sup> /2	21½	4	61.5	
8	4	10	11	275/8	51/4	98.8	
8	6	10	11	275/8	5 <sup>1</sup> /4	99.7	
10	8	12	13	315/8	6 <sup>1</sup> /4	187.0	
12	10	15	15	383⁄4	71/4	287.6	
15	12	18½	18½	45	9	460.0	



S E R V I C E