



Press X Press Full Port Ball Valve

NSF

NSF 61-8



JP-100PxP

Description

1/4 turn, lever operated, corrosion resistant (CR) forged brass ball valve. 100% full port. Blow-out proof two-piece design. Made in Italy. 100% tested.

Features

- Press fit ends for fast, reliable installation
- Pressure rating: 250 WOG
- Temperature rating: max. 250° F
- CuZn36Pb2As Dezincification-resistant Brass (CR)
- Drilled ball to prevent bursting and proliferation of bacteria
- Triple sealing stem with Viton® O-rings and Teflon® seal
- EDPM O-rings

Approvals

- NSF 61-8 certified - tested at 180° F (commercial hot water)

Warranty

The Company, for a period of one year from the date of shipment, warrants each product or system of its own manufacture to the original purchaser to be free from defects in material and workmanship under normal use, service and maintenance.

Architect/Engineer approval

Job Name _____ Date _____
Model Specified _____ Quantity _____
Variations Specified _____
Customer/Wholesaler _____
Contractor _____
Architect _____

Note: Information subject to change without notice.



Jomar Valve
7243 Miller Drive
Warren, MI 48092
Phone: 800-325-5690
Fax: 800-628-4194
www.jomarvalve.com

JP-100PxP
© Copyright 2010 Printed in U.S.A.
0510

Press X Press
Full Port Ball Valve



Description

1/4 turn, lever operated, corrosion resistant (CR) forged brass ball valve. 100% full port. Blow-out proof two-piece design. Made in Italy. 100% tested.

Dimensions in Inches



Computer No.	Valve Size	A	B	C	D
100-203	1/2"	3.54	1.53	2.95	1.24
100-204	3/4"	3.84	1.92	3.74	1.28
100-205	1"	4.31	2.40	4.72	1.38
100-206	1-1/4"	4.80	2.59	4.72	1.30
100-207	1-1/2"	5.61	3.22	5.90	1.50
100-208	2"	7.16	3.50	5.90	2.01

Material Specification

No.	Part Name	Materials
1	Body	Corrosion Resistant Forged Brass
2	End Piece	Corrosion Resistant Forged Brass
3	Special Solid "T" Ball	Diamond Polished TEA Coated Brass
4	Seat (2)	Hostaflon®-TFM 1600
5	Stern	Corrosion Resistant Forged Brass
6	Stern O-ring (2)	Viton®
7	Stern Packing	Hostaflon®-TFM 1600
8	Packing Nut	Corrosion Resistant Forged Brass
9	Lever Handle	Dacromet Coated Steel
10	Handle	Dacromet Coated Steel
11	O-ring (2)	EPDM

Pressure Rating

250 WOG



Note: Information subject to change without notice.



Jomar Valve
7243 Miller Drive
Warren, MI 48092
Phone: 800-325-5690
Fax: 800-628-4194
www.jomarvalve.com