

Type



-77 -81

P2730 ☐ ☐

P2731 ☐ ☐

P2732 ☐ ☐

Catalog No.	Finish		Lamping	Dimensions (Inches)			
	Espresso	Nickel		A	B	C	D
P2730	-77	-81	2 (m) 100w	14	8-1/4	8-1/8	5-3/8
P2731	-77	-81	3 (m) 100w	22	8-1/4	8-1/8	5-3/8
P2732	-77	-81	4 (m) 100w	30	8-1/4	8-1/8	5-3/8



Specifications:

General

- Etched glass shade
- Can be mounted in "up" or "down" position
- Steel construction
- Hand painted forged bronze or plated antique nickel finish
- Companion chandeliers, hall & foyer, wall bracket, pendant, sconce and close to ceiling units

Mounting

- Wall mounted
- Back plate covers a standard recessed 4" octagonal outlet box
- Mounting strap for outlet box included
- Threaded socket ring secures glass

Electrical

- Ceramic medium based sockets
- Pre-wired

Labeling

- UL-CUL damp location listed