



\*height from center of outlet to the top of the fixture

Measurements:

<u>Height</u>	<u>Width</u>	<u>Extension</u>
24.50"	10.00"	13.00"
<u>BP Height</u>	<u>BP Width</u>	<u>HCO</u>
15.75"	7.00"	13.50"
<u>Hanging Weight</u>		
4.58 lb		

Lamping:

Incandescent CA	2,016 Rated Lumens
3.00 40W CA	Color Temperature
120 total watt	1,500 Rated Life
Dimmable : Standard Dimmer	

Shipping:

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
6.78 lb	11.61"	34.84"	16.73"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
1.0000	783209302402	Yes	

Finish:

Bronze BZ

Glass:

Seedy CD

Material:

Die Cast Aluminum

Certification:

Wet Location  
Location

Additional:

CA (Not Included)