

Company name: Created by: Phone:

Date: 10/30/2020

Count 1

Description

UPS 26-99 FC



Product photo could vary from the actual product

Product No.: 52722512

The pump is of the canned rotor type, i.e. pump and motor form an integral unit without shaft seal and with only two gaskets for sealing.

The bearings are lubricated by the pumped liquid.

The pump is characterized by:

* Ceramic shaft and radial bearings.

* Carbon axial bearing.

* Stainless steel rotor can and bearing plate.

Impeller: * Corrosion-resistant impeller, Composite, PES.

Pump housing: * Cast iron pump housing.

Phase: The motor is a 1-phase motor.

No additional motor protection is required.

Liquid:

Pumped liquid: Water
Liquid temperature range: 35.6 .. 230 °F
Selected liquid temperature: 140 °F
Density: 61.35 lb/ft³

Technical:

Approvals on nameplate: UL, CSA

Materials:

Pump housing: Cast iron

EN-JL1030 ASTM 30 B

Impeller: Composite, PES

Installation:

Maximum ambient temperature: 104 °F
Ambient max at 176°F liquid: 176 °F
Maximum operating pressure: 145.04 psi
Flange standard: USA Oval
Type of connection: C.I. Flange
Pipe connection: 2 - Bolt Flange

Pressure stage: PN 10
Port-to-port length: 6 1/2 in

Electrical data:

Power input in speed 1: 0.2012 HP Power input in speed 2: 179 W



Company name: Created by: Phone:

			Date:	10/30/2020	
unt	Description				
	Max. power input: Main frequency: Rated voltage: Current in speed 1: Current in speed 2: Current in speed 3: Capacitor size - run: Number of poles: Insulation class (IEC 85):	197 W 60 Hz 1 x 115 V 1.3 A 1.5 A 1.8 A 20 μF/180 V 2			
	Others: Gross weight: Country of origin: Custom tariff no.:	10.3 lb US 8413.70.2005			



Company name: Created by: Phone:

Date:	10/30/2020

Description	Value
General information:	Taido
Product name:	UPS 26-99 FC
Product No.:	52722512
EAN:	5700834818707
Price:	0,000,10,10,10,1
Technical:	
Speed Number:	3
Maximum flow:	33 US gpm
Max flow:	33 US gpm
Maximum head:	28.87 ft
Head max:	28.87 ft
Approvals on nameplate:	UL, CSA
Approvate on namepiate.	pump with built-in isolating and
Valve:	non-return valves
Materials:	04:
Pump housing:	Cast iron
Pump housing:	EN-JL1030
Pump housing:	ASTM 30 B
Impeller:	Composite, PES
Installation:	
Maximum ambient temperature:	104 °F
Ambient max at 176°F liquid:	176 °F
Maximum operating pressure:	145.04 psi
Flange standard:	USA Oval
Type of connection:	C.I. Flange
Pipe connection:	2 - Bolt Flange
Pressure stage:	PN 10
Port-to-port length:	6 1/2 in
Liquid:	
Pumped liquid:	Water
Liquid temperature range:	35.6 230 °F
Selected liquid temperature:	140 °F
Density:	61.35 lb/ft ³
Electrical data:	
Power input in speed 1:	0.2012 HP
Power input in speed 2:	179 W
Max. power input:	197 W
Main frequency:	60 Hz
Rated voltage:	1 x 115 V
Current in speed 1:	1.3 A
Current in speed 2:	1.5 A
Current in speed 3:	1.8 A
Capacitor size - run:	20 μF/180 V
Number of poles:	2
Insulation class (IEC 85):	F
Motor protection:	CONTACT
Thermal protec:	internal
Controls:	
Pos term box:	9H
Others:	-
Gross weight:	10.3 lb
Country of origin:	US
Custom tariff no.:	8413.70.2005
Gustoiii taiiii iio	UT 13.7 U.ZUUJ





