



VITREOUS CHINA

TOILET
21-810

LAVATORIES

TOILETS

BIDETS / URINALS

CAST IRON

AVALANCHE™ Elongated Toilet

10" Rough-in

Features:

- 1.6 gpf (6.0 Lpf)
- Elongated Bowl
- Slim Line Tank
- Gerber XP-3 Technology
- Fluidmaster® Fill Valve
- 3" Flush Valve
- Glazed Trapway
- Reverse Trap
- Dual Feed Jet
- Side Tank Lever
- White, Bone and Biscuit
- 2 Bolt Caps


Dimensions:

Height 28 5/8"
Width 17"
Depth 28"
Rough-in 10"
Water Surface from Rim 5 1/2"
Trapway (min) 2"
Water Surface 11 1/8" x 8 7/8"
Water Seal 2 3/8"
Shipping Weight 80 lbs



Specifications: Bowl—#21-862 Elongated Bowl
Seat not included

Tank—#28-895




THIS FIXTURE QUALIFIES
ACCORDING TO ASME TEST
PROCEDURES AS A WATER CLOSET
WITH AN AVERAGE CONSUMPTION
OF 1.6 GAL. OR LESS.



www.gerberonline.com

Job Name	
Date	
Model Specified	
Quantity	
Customer	
Contractor	
Architect/engineer	



NOTES:

All dimensions are in inches.

Illustrations may not be drawn to scale.

IMPORTANT:

Dimensions of fixtures are nominal and may vary within the range of tolerances established by ASME Standard A 112.19.2.

THIS FIXTURE QUALIFIES ACCORDING TO ASME
TEST PROCEDURES AS A WATER CLOSET WITH AN
AVERAGE CONSUMPTION OF 1.6 gpf (6 Lpf) OR LESS.