


**IPS FAB 2 SEG. 45 ELBOW**

PE4710

<u>Nominal Size</u> <u>Actual OD</u>	<u>Pressure Class (psi)</u>	<u>Feed Stock</u>	<u>Dimension</u> <u>R x C x B (in)</u>	<u>Weight per</u> <u>Item (lbs)</u>	<u>Part #</u>
<b>8"</b> 8.630"	100	DR 17	10 5/8 x 6 1/2 x 8 1/4	9	PEI17HB4XF2
	160	DR 11		13	PEI11HB4XF2
	200	DR 9		15	PEI9HB4XF2
	250	DR 7		19	
<b>10"</b> 10.750"	100	DR 17	12 5/8 x 6 1/2 x 8 3/4	12	PEI17HB410F2
	160	DR 11		18	PEI11HB410F2
	200	DR 9		22	PEI9HB410F2
	250	DR 7		26	PEI7HB410F2
<b>12"</b> 12.750"	100	DR 17	13 5/8 x 8 x 10 5/8	21	PEI17HB412F2
	160	DR 11		32	PEI11HB412F2
	200	DR 9		38	PEI9HB412F2
	250	DR 7		45	PEI7HB412F2
<b>14"</b> 14.000"	100	DR 17	14 1/4 x 8 x 10 7/8	27	PEI17HB414F2
	160	DR 11		40	PEI11HB414F2
	200	DR 9		48	PEI9HB414F2
	250	DR 7		58	PEI7HB414F2
<b>16"</b> 16.000"	100	DR 17	15 1/4 x 8 x 11 5/16	37	PEI17HB416F2
	160	DR 11		55	PEI11HB416F2
	200	DR 9		66	PEI9HB416F2
	250	DR 7		79	PEI7HB416F2
<b>18"</b> 18.000"	100	DR 17	16 1/4 x 8 x 11 3/4	47	PEI17HB418F2
	160	DR 11		70	PEI11HB418F2
	200	DR 9		83	PEI9HB418F2
	250	DR 7		100	PEI7HB418F2
<b>20"</b> 20.000"	100	DR 17	17 1/4 x 8 x 12 1/8	60	PEI17HB420F2
	160	DR 11		90	PEI11HB420F2
	200	DR 9		108	PEI9HB420F2
	250	DR 7		129	PEI7HB420F2
<b>22"</b> 22.000"	100	DR 17	23 1/16 x 8 x 12 9/16	76	PEI17HB422F2
	160	DR 11		114	PEI11HB422F2
	200	DR 9		136	PEI9HB422F2
	250	DR 7		162	PEI7HB422F2



**IPS FAB 2 SEG. 45 ELBOW**

PE4710

<u>Nominal Size</u> <u>Actual OD</u>	<u>Pressure Class (psi)</u>	<u>Feed Stock</u>	<u>Dimension R x C x B (in)</u>	<u>Weight per Item (lbs)</u>	<u>Part #</u>
<b>24"</b> 24.000"	100	DR 17	24 1/16 x 8 x 13	94	PEI17HB424F2
	160	DR 11		141	PEI11HB424F2
	200	DR 9		168	PEI9HB424F2
	250	DR 7		201	PEI7HB424F2
<b>28"</b> 28.000"	100	DR 17	38 3/16 x 14 x 19 13/16	198	PEI17HB428F2
	160	DR 11		295	PEI11HB428F2
	200	DR 9		353	PEI9HB428F2
<b>30"</b> 30.000"	100	DR 17	38 5/16 x 14 x 20 3/16	228	PEI17HB430F2
	160	DR 11		339	PEI11HB430F2
	200	DR 9		405	PEI9HB430F2
<b>32"</b> 32.000"	100	DR 17	38 3/8 x 14 x 20 5/8	266	PEI17HB432F2
	160	DR 11		396	PEI11HB432F2
<b>34"</b> 34.000"	100	DR 17	38 7/16 x 14 x 21 1/16	307	PEI17HB434F2
	160	DR 11		458	PEI11HB434F2
<b>36"</b> 36.000"	100	DR 17	38 1/2 x 14 x 21 7/16	353	PEI17HB436F2
	160	DR 11		525	PEI11HB436F2
<b>42"</b> 42.000"	80	DR 21	50 5/16 x 21 x 29 11/16	513	PEI21HB442F2
	100	DR 17		659	PEI17HB442F2
<b>48"</b> 48.000"	80	DR 21	50 9/16 x 21 x 30 15/16	742	PEI21HB448F2
	100	DR 17		905	PEI17HB448F2
<b>54"</b> 54.000"	65	DR 26	50 3/4 x 21 x 32 3/16	775	PEI26HB454F2
	80	DR 21		969	PEI21HB454F2