



PE4710

DIPS FAB 2 SEG. 45 ELBOW

<u>Nominal Size</u> <u>Actual OD</u>	<u>Pressure</u> <u>Class (psi)</u>	<u>Feed</u> <u>Stock</u>	<u>Dimension</u> <u>R x C x B (in)</u>	<u>Weight per</u> <u>Item (lbs)</u>	<u>Part #</u>
4" 4.800"	80	DR 17	6 x 5 1/2 x 6 1/2		
	160	DR 11		3	PED11HB4PF2
	200	DR 9		4	PED9HB4PF2
	250	DR 7		5	PED7HB4PF2
6" 6.900"	80	DR 17	9 1/2 x 6 x 7 3/8		
	160	DR 11		8	PED11HB4UF2
	200	DR 9		9	PED9HB4UF2
	250	DR 7		10	PED7HB4UF2
8" 9.050"	80	DR 17	10 1/2 x 6 1/2 x 8 3/8		
	160	DR 11		15	PED11HB4XF2
	200	DR 9		18	PED9HB4XF2
	250	DR 7		20	PED7HB4XF2
10" 11.100"	100	DR 17	12 3/4 x 6 1/2 x 10 3/4	16	PED17HB410F2
	160	DR 11		24	PED11HB410F2
	200	DR 9		29	PED9HB410F2
	250	DR 7		38	
12" 13.200"	100	DR 17	13 7/8 x 8 1/2 x 11 1/4	27	PED17HB412F2
	160	DR 11		40	PED11HB412F2
	200	DR 9		48	PED9HB412F2
	250	DR 7		54	PED7HB412F2
14" 15.300"	100	DR 17	14 7/8 x 8 1/2 x 11 5/8	34	PED17HB414F2
	160	DR 11		50	PED11HB414F2
	200	DR 9		60	PED9HB414F2
	250	DR 7		75	PED7HB414F2
16" 17.400"	100	DR 17	16 x 8 1/2 x 13 5/8	55	PED17HB416F2
	160	DR 11		82	PED11HB416F2
	200	DR 9		97	PED9HB416F2
	250	DR 7		114	PED7HB416F2
18" 19.500"	100	DR 17	17 X 8 1/2 X14	73	
	160	DR 11		108	PED11HB418F2
	200	DR 9		129	PED9HB418F2
	250	DR 7		148	
20" 21.600"	100	DR 17	22 7/8 X 8 1/2 X14 1/2	101	PED17HB420F2
	160	DR 11		128	PED11HB420F2
	200	DR 9		152	PED9HB420F2
	250	DR 7		189	
24" 25.800"	100	DR 17	25 X 8 1/2 X15 3/8	157	PED17HB424F2
	160	DR 11		195	PED11HB424F2
	200	DR 9		233	PED9HB424F2
	250	DR 7		288	PED7HB424F2

DIPS FAB 2 SEG

45 ELL

Printed copy not
controlled

Dimensions and weights are approximate and subject to change

Rev 1 02/17/2016