## PFTG92352

# **Cast Iron** Submersible Pumps


### Product Features

- 1/3 HP cast iron submersible sump pump with side discharge - vertical float
- Submersible sump pump for typical residential and commercial applications
- · Comes with 10' power cord
- 7.6 amps, 912 watts
- Maximum head of 25 feet
- Maximum flow rate of 60 GPM



PROFLO.





#### **Performance Chart**

Discharge Height	0'	5'	10'	15'	20'	25'
Gallons per Minute	60	56	50	35	15	6
Gallons per Hour	3600	3360	3000	2100	900	360

#### Warranty and Codes

This product comes complete with installation, operating, care and maintenance instructions. This PROFLO pump carries a 5-year limited warranty. In an effort to continually improve our products, we will make design changes from time to time. We reserve the right to ship newly designed products to fill any order unless we agree in writing to do otherwise.

Includes check valve,

switch

32°-120°F

ABS discharge pipe & base

· SJE Rhombus vertical float

• Liquid temperature range

Discharge size 1-1/2" FNPT

• Handles 1/2" solids

· Permanent split capacitor motor

