# Specifications

# *PF92501 Cast Iron Sump Pump*



## **Product Features**

- Rugged cast iron pump body for durability
- SJE Rhombus tethered float switch
- 1-1/2" NPT Discharge
- Handles up to 1/2" solids
- Clog resistant impeller
- Carrying handle attached

- 10' power supply cord
- Built-in thermal overload protection for safety
- Permanent split capacitor
- continuous duty motor7.6 amps, 708 Watts
- 3450 RPM




PF92501

#### Motor Performance

• 1/2 HP 120 Volt AC (7.6 amps)

Performance Chart						
Lift	0'	5'	10'	15'	20'	25'
GPM GPH	70 4200	66 3960	58 3480	48 2880	25 1500	10 600
L u u	4200	5500	5400	2000	1300	000

### **Product Specifications**



\* All measurements are nominal. Please verify before actual installation.

#### Warranty and Codes

This product comes complete with installation, operating, care and maintenance instructions. This PROFLO sump pump carries a 5 year warranty when installed in residential applications. See owners manual for warranty details.

This PROFLO sump pump carries a 5 year limited warranty. In an effort to continually improve our products, we will make design changes from time to time. We reserve the right to ship newly designed product to fill any order unless it is agreed in writing to do otherwise.

