



## Commercial Grade Striplight S Series

LOCATION		DATE
PREPARED BY		QUANTITY
COMMENTS		FIXTURE TYPE
CATALOG NUMBER		

### Features

Functional and multi-purpose standard 1 or 2 light strip channel provides general illumination for indoor and damp applications. Product features include snap assembly of ends, socket bars and wire way cover and requires no tools. Fixture can be mounted individually or in continuous rows for surface or suspended mounting. Applications include light commercial, industrial, retail, coves and displays.

### Construction

Heavy-duty channel is die-formed from 22-gauge steel. Channel cover snaps to housing for easy access to wire way. Electrical connections are made inside the wire way. Standard mounting holes and wiring knockouts are included.

### Finish

Housing is finished in lighting grade white baked gloss enamel paint.

### Diffuser

No diffuser for this fixture. Fluorescent lamps are exposed.

### Electrical

This unit can be ordered in the following options: with UL listed instant-start, electronic high power factor ballast; 120V 60Hz AC (E12, E8 suffix), 120-277 Universal 50/60Hz AC (MV suffix).

### Lamping

For use with T12 fluorescent linear lamps (E12) or for use with T8 slimline linear lamps (E8, MV); supplied by others.

### Certification


All fixtures are cULus listed for damp location.

### Options (consult factory)

Reflectors  
Fusing  
Dimming  
Emergency battery back-up

For photometric information, consult factory.

Specifications and dimensions  
subject to change without notice.



## Ordering Information:

Model No.	Lamps				Dimensions			
430 mA-Slimline	120V T12	120V T8	120-277V	Qty	Type	L	W	D
	S196E12	S196E8		1	F96T12	96"	4-1/4"	3-3/4"
				1	F96T8	96"	4-1/4"	3-3/4"
	S248E12			2	F48T12	48"	4-1/4"	3-3/4"
	S272E12	S272E8		2	F72T12	72"	4-1/4"	3-3/4"
				2	F72T8	72"	4-1/4"	3-3/4"
	S296E12			2	F96T12	96"	4-1/4"	3-3/4"
		S296E8	S296MV	2	F96T8	96"	4-1/4"	3-3/4"
800 mA-High Output 20°F	120V T12	120V T8		Qty	Type	L	W	D
	S196HOE12			1	F96T12HO	96"	4-1/4"	3-3/4"
	S248HOE12			2	F48T12HO	48"	4-1/4"	3-3/4"
	S272HOE12			2	F72T12HO	72"	4-1/4"	3-3/4"
	S296HOCWE12			2	F96T12HO-O	96"	4-1/4"	3-3/4"
		S296HOE8		2	F96T8HO	96"	4-1/4"	3-3/4"