



Square Edged Floating Cloud MAR232/240/432/440

Features

The molded white cloud diffuser has a box style shape with rounded corners and edges for a softer appearance. Fixture is available in two sizes, 9-3/4" x 50", and 16-1/4" x 50". It can be used in various applications including corridors, kitchens and public spaces. Fixture mounts to standard junction box (not included).

Construction

Housing is die-formed of 22-gauge steel. Standard mounting holes are included. Power supply connections can be made inside the fixture wire way or in a junction box (not included).

Finish

Back plate is finished in lighting grade white baked gloss enamel paint.

Diffuser

Diffuser is formed from a sheet of cast white acrylic plastic. Four clips on the two edges of the diffuser allow it to lift and shift for easy removal.

Electrical

This unit can be ordered in the following options: with UL listed instant-start, electronic high power factor ballast; 120V 60Hz AC (E8 suffix), 120-277 Universal 50/60Hz AC (MV suffix). R8 model number suffix designates normal power factor, 120V, residential grade ballast.

Lamping

For use with 2/32, or 4/32 watt T8 linear fluorescent lamps; supplied by others.

Certification

All fixtures are cULus listed for damp locations.


Options (consult factory)

120-277V HPF
Dimming
Emergency battery back-up

For photometric information, consult factory.

Specifications and dimensions
subject to change without notice.

Project		Fixture Type
Location		Quantity
Approved By	Date	Catalog Number



Ordering Information:

Model No.				Lamps		Dimensions			Mounting
Finish	120V	120V	120-277V	Qty	Lamp	H	W	L	M
White Diffuser	MAR232R8	MAR240E8	MAR232MV	2	F32T8	3-5/8"	9-3/4"	50"	35"
White Diffuser	MAR432R8	MAR440E8	MAR432MV	4	F32T8	3-5/8"	16-1/4"	50"	35"