

Highline® Pressure Lite® Toilet K-3519-RA

Features

- Vitreous china.
- Elongated bowl
- Equipped with Sloan FLUSHMATE®— Sloan® Valve Company.
- Polished chrome trip lever.
- Less seat and supply.
- 12" (305 mm) rough-in.
- 1.0 gpf (3.8 lpf).
- 2-1/4" (57 mm) glazed trapway.
- 11-1/2" (292 mm) x 9-1/2" (241 mm) water area.
- 30-1/8" (765 mm) x 21-1/4" (540 mm) x 31-1/4" (794 mm).

Recommended Accessories

K- 4650 Toilet Seat 4664

K- 7637 Angle Supply with Stop (single)

Components

Product includes:

K- 4304 Toilet Bowl

K- 4484-RA Toilet Tank

Additional included component/s: Tank cover, and Trip lever.





ADA CSA B651

OBC

DA CSA B651 U

Codes/Standards

ASME A112.19.2/CSA B45.1 DOE - Energy Policy Act 1992 EPA WaterSense® ADA ICC/ANSI A117.1 CSA B651 OBC

KOHLER® One-Year Limited Warranty

See website for detailed warranty information.

Available Color/Finishes

Color tiles intended for reference only.


Color	Code	Description
	0	White
	96	Biscuit
	47	Almond
	7	Black Black™





Highline®

Pressure Lite® Toilet K-3519-RA



Technical Information

All product dimensions are nominal.

Toilet type: Two-piece

Bowl shape: Elongated front

Flush type: Programs Assists

Flush type: Pressure Assisted Trap passageway: 2-1/4" (57 mm)

Water surface size: 11-1/2" x 9-1/2" (292 mm x 241 mm)

Rim to water surface: 5-3/4" (146 mm)
Rough-in: 12" (305 mm)
Seat-mounting holes: 5-1/2" (140 mm)

Fixture Supply Requirements

Min static pressure: 35 psi (241.3 kPa) Max static pressure: 80 psi (551.6 kPa)

Notes

Install this product according to the installation quide.

For back-to-back toilet installations: Use only a 45° double wye fitting.

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.

The Model Plumbing Codes require the installation of elongated open-front toilet seats on public bathrooms.

